


- Handwheel
- Material: aluminium
- Finish: edges machined and polished
- Keyway conforms to DIN6885-1

Advantages

- Light

Options

- A version with a handle exists, see HLU T



DISCOUNTS

Qty	1+	6+	15+	20+
Disc.	List	-5%	-10%	On request


Part number		ØD1	ØD2 (H7)	ØD3	L1	L3	B3 (P9)	T	Stock* with keyway	Stock* without keyway	Price each 1 to 5	
with keyway	without keyway										with keyway	without keyway
With 3 spokes												
HLU80-10K	HLU80-10	80	10	24	16	29	3	11,4	-	-	18,15 €	15,48 €
HLU100-10K	HLU100-10	100	10	26	17	33	3	11,4	✓	-	19,89 €	16,93 €
HLU125-12K	HLU125-12	125	12	28	18	36	4	13,8	✓	✓	24,42 €	21,22 €
HLU140-14K	HLU140-14	140	14	30	19	39	5	16,3	✓	-	28,59 €	25,35 €
HLU160-14K	HLU160-14	160	14	32	20	40	5	16,3	-	-	33,46 €	30,04 €
HLU180-16K	HLU180-16	180	16	35	22	43	5	18,3	-	-	39,73 €	36,27 €
HLU200-18K	HLU200-18	200	18	38	24	45	6	20,8	✓	-	48,57 €	44,88 €
With 5 spokes												
HLU250-22K	HLU250-22	250	22	45	28	50	6	24,8	-	✓	78,50 €	73,69 €
HLU315-26K	HLU315-26	315	26	53	33	56	8	29,3	-	-	122,90 €	118,18 €
HLU400-30K	HLU400-30	400	30	65	38	63	8	33,3	-	-	225,22 €	218,12 €
HLU500-34K	HLU500-34	500	34	78	45	72	10	37,3	-	-	376,48 €	367,69 €

*Depending on availability - Dimensions in mm

Our other products



BLH70
Right angled gearbox,
from 26 to 128 Nm



PF20NM
Worm and wheel gear
reducer, up to 5 Nm



AC156-157
Strike for toggle latch,
25.5mm



F7-SF-SM
Multifunction display,
Mounting bracket for
front mounting



SBF
Sealed flange bearing
unit for Food Industry,
cover



RJUM01
Closed polymer
Drylin® R bearing,
Drylin® R




HLC19
Right angle spiro
bevel gearbox, Up to
43Nm



GCL
Linear ball slide -
Stainless steel balls,
Chariot - from 516 N
to 8...



MAX22
Motor-gearbox 12V
and 24V DC, from



Q3
Double row angular
contact ball bearing,



T10_30_AL
T type timing pulley,
Economy range - T10



PW_PWG1
Worm - precision
range, Stainless steel

Complementary products



HLUT
Spoked handwheel
with handle,
Aluminium



HLUsS
Spoked handwheel,
Stainless steel 316