

180° ball and socket joint steel or stainless steel Stock Ste

IBJ Steel/steel or stainless steel/stainless steel contact

IBJss

- **Inline ball and socket joint similar to DIN 71802**

- Body to DIN 71805

- Stem to DIN 71803


- Materials:

Zync plated steel

Stainless steel 1.4305 (A2 stainless steel)



Steel or
stainless steel



NEW
DISCOUNTS

DISCOUNTS **A** / steel

Qty	1+	6+	20+	40+	60+
Disc.	Price	-20%	-30%	-50%	On request

DISCOUNTS **B** / stainless steel

Qty	1+	6+	20+	40+	60+
Disc.	Price	-15%	-20%	-30%	On request

Part number	ØD	ØT	A	L1	L3	E	SW	Axial load F (N)	Weight (kg)	Stock*	Price each 1 to 5
Steel											
IBJ-5	8	M5	22	19,2	9	10,2	7	30	0,015	✓	A 5,35 €
IBJ-6	10	M6	25	23,5	11	11,5	8	40	0,025	✓	A 6,86 €
IBJ-8	13	M8	30	29,5	13	14,0	11	60	0,053	✓	A 7,25 €
IBJ-10	16	M10	35	36,0	16	15,5	13	80	0,104	✓	A 10,05 €
IBJ-14x1.5	19	M14x1,5	45	48,0	20	21,5	16	100	0,221	✓	A 25,66 €
Stainless Steel											
IBJ-5/SS	8	M5	22	19,2	9	10,2	7	30	0,015	✓	B 9,64 €
IBJ-6/SS	10	M6	25	23,5	11	11,5	8	40	0,025	✓	B 11,55 €
IBJ-8/SS	13	M8	30	29,5	13	14,0	11	60	0,055	✓	B 12,68 €
IBJ-10/SS	16	M10	35	36,0	16	15,5	13	80	0,105	-	B 20,76 €

*Depending on availability - Dimensions in mm

Our other products



ACLEPP
Right angled bracket for aluminium profile, 4 holes



GMK17_RG
Joint for guiding profile, Rounded



PRF_CLIP_22
Cable clip for aluminium profile, For electric and pneumatic cables



UCF_PBT
Stainless steel/Polymer flanged bearing, Polymer and stainless steel




PSPE22
Conical flexible shaft handle Ø22, Black PVC



CHINV
Invisible hinge, Invisible - Opening up to 90°




M0
Worm and wheel set, Bronze



IN2
Internal gear, Machined plastic (delrin)



JCDss
Double universal joint - Stainless steel, Low duty



CAB
Stainless steel cable, Stainless steel



MRA_SS
Stainless steel Quick link, Stainless steel



CFF_SS
Female rod ends DIN ISO12240-4, Stainless steel / bronze - Economy r...

Complementary products



RAS
90° ball and socket joints DIN71802, Steel



IBJss
Ball and socket joint, Stainless steel



CNA-CNG
Right angled mounting plate, Right angled mounting plate for ball jo...