
- ***Pressure angle 20°***
- *Materials:*
  steel 34C10 or
  delrin plastic (machined parts)



IN: Steel




ZIN: Plastic

Options

- ***Alternative number of teeth (minimum 58 teeth)***
- *Alternative materials (stainless steel, brass..)*

Accessories

- *Spur gears with the same module eg* **G1.25**.., **ZG1.25**..





STEEL DISCOUNTS

Qty.	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

PLASTIC DISCOUNTS

Qty.	1+	6+	30+
Disc.	List	-22%	On request

STEEL *IN*	PLASTIC *ZIN*	Z Teeth	PCD ØP	Part number Internal ØA	ØD	Boss ØM	Price each 1 to 5 STEEL *IN*	PLASTIC *ZIN*
IN1.25-51	ZIN1.25-51	51	63,75	61,75	100	94	62,55 €	45,04 €
IN1.25-60	ZIN1.25-60	60	75,00	72,50	100	94	67,05 €	48,28 €
IN1.25-100	ZIN1.25-100	100	125,00	122,50	175	150	117,31 €	84,46 €
↓	↓	**Gears available up to this size**					↓	↓
IN1,25-160	**ZIN1,25-160**	**160**	**200,00**	**197,50**	**250**	**225**	**on request**	**on request**

Dimensions in mm

Our other products


CHAE6555

Decorative screwed hinge, Aluminium


PRES7HR

Manual workbench press, Force up to 700kg


GARBAB

Lock pin for clamping, Ball lock pin


PLB

Cylindrical spacer, Brass


GCB880

Curved track for slat top chain, Ranges 880 and 881


RHTplss

High Temperature Castor, up to 200kg


SHTC

Drylin® Linear table, Maintenance free



KB_UU

Closed linear precision bearing, Precision - steel


PRF_P

Anchor foot for 45x45 profile, Anchor foot


CLSCLP

Clevis components, short version, Steel -


VAB

Ballscrew, supplied by the metre, Rolled


PRF_JL5

Lip seal for panel, Door seal - Ø 5mm

Complementary products


ZG125

Plastic spur gear, Machined plastic (delrin)