Internal gear

MODULE 1.0

Steel or machined plastic

- ***Pressure angle 20°***
- *Materials:*
  steel 34C10 or
  delrin plastic (machined parts)

Options

- ***Alternative number of teeth (minimum 58 teeth)***
- *Alternative materials (stainless steel, brass..)*

Accessories

- *Spur gears with the same module eg* **G1**.., **ZG1**..



IN: Steel



ZIN: Plastic



STEEL DISCOUNTS

Qty.	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

PLASTIC DISCOUNTS

Qty.	1+	6+	30+
Disc.	List	-22%	On request

STEEL *IN*	PLASTIC *ZIN*	Z Teeth	PCD ØP	Part number Internal ØA	ØD	Boss ØM	Price each 1 to 5 STEEL *IN*	Price each 1 to 5 PLASTIC *ZIN*
IN1-58	ZIN1-58	58	58	56	100	94	60,97 €	43,90 €
IN1-60	ZIN1-60	60	60	58	100	94	61,75 €	44,45 €
IN1-100	ZIN1-100	100	100	98	150	125	105,97 €	76,29 €
↓	↓	Gears available up to this size					↓	↓
IN1-200	**ZIN1-200**	**200**	**200**	**198**	**250**	**225**	**on request**	**on request**

Dimensions in mm

Our other products

BH01

Single housed bearing, Bearing fitted with adhesive

PSG15

Spur gear - precision range, Case hardened steel 20NCD2

EAR

Bearing locknut, Self locking locknut - nylon lock washer

MSP23

Masterplate® glueable insert Ø23, Cylindrical Ø23 with threaded s...

SER

Magnetic doorstop for aluminium profile, Magnetic doorstop

PRF_ECL

Nut for aluminium profile, Steel square nut with tab

AT5M_AT10M

AT type timing belt per metre, AT5 Steel cored polyurethane

CDGamme

Compression spring DIN2095, DIN 2095

BABFCFO

Ball pin socket, Mounting collar with a

PTRSS

Idler chain sprocket, For hostile

GP

Spring loaded toggle latch, Standard

G1

Steel spur gear, Steel 20NCD2

Complementary products

IN1

Internal gear, Steel 20NCD2

ZG1

Plastic spur gear, Machined plastic (delrin)

CLG1

Moulded plastic spur gear, Moulded plastic (nylon)