Internal gear

MODULE 1.0

Steel or machined plastic


- ***Pressure angle 20°***
- *Materials:*
  steel 34C10 or
  delrin plastic (machined parts)

Options

- ***Alternative number of teeth (minimum 58 teeth)***
- *Alternative materials (stainless steel, brass..)*

Accessories


- *Spur gears with the same module eg* **G1**.., **ZG1**..



IN: Steel



ZIN: Plastic



bore-size, keyway
MODIFY IT!
tapped hole, pin, etc...

STEEL DISCOUNTS

Qty.	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

PLASTIC DISCOUNTS

Qty.	1+	6+	30+
Disc.	List	-22%	On request

STEEL *IN*	PLASTIC *ZIN*	Z Teeth	PCD ØP	Part number Internal ØA	ØD	Boss ØM	Price each 1 to 5 STEEL *IN*	Price each 1 to 5 PLASTIC *ZIN*
IN1-58	ZIN1-58	58	58	56	100	94	60,97 €	43,90 €
IN1-60	ZIN1-60	60	60	58	100	94	61,75 €	44,45 €
IN1-100	ZIN1-100	100	100	98	150	125	105,97 €	76,29 €
↓	↓	Gears available up to this size					↓	↓
IN1-200	**ZIN1-200**	**200**	**200**	**198**	**250**	**225**	**on request**	**on request**

Dimensions in mm

Our other products


BOX-TOR-H


Box set of Nitrile O-rings in nitrile, 3.00 x 2.00mm to 45.20 x 4.00


BCM_TP

Modular cylindrical brush, Tampico bristles


ZG0

Plastic spur gear, Machined plastic (delrin)


LAT2


2A motorised linear actuator, 2 amperes


ZG2

Plastic spur gear, Machined plastic (delrin)


DB

Steel bevel gear, 2:1


M0

Worm and wheel set, Machined plastic (delrin)


MHPGR

Arm with folding rotating handle,


G0

Steel spur gear, Steel 20NCD2


PX

Optional output shaft stainless steel, P gearboxes single



DOG316

Motor-gearbox 12V and 24V DC, from 1.5 to 2 Nm


CHMR50

Worm and wheel gear reducer, up to 107 Nm

Complementary products


IN1

Internal gear, Machined plastic (delrin)


G1

Steel spur gear, Steel 20NCD2


GG1

Ground spur gear, Heat treated steel