Internal gear

Steel or machined plastic

MODULE 2.0

- ***Pressure angle 20°***
- *Materials:*
  steel 34C10 or
  delrin plastic (machined parts)

Options


- ***Alternative number of teeth***
- *Alternative materials (stainless steel, brass..)*

Accessories

- *Spur gears with the same module eg* **G2**.., **ZG2**..




IN: Steel



ZIN: Plastic

NEW!

bore-size, keyway
MODIFY IT!
tapped hole, pin, etc...



STEEL DISCOUNTS

Qty.	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

PLASTIC DISCOUNTS

Qty.	1+	6+	30+
Disc.	List	-22%	On request

STEEL *IN*	PLASTIC *ZIN*	Z Teeth	PCD ØP	Part number Internal ØA	ØD	Boss ØM	Price each 1 to 5 STEEL *IN*	PLASTIC *ZIN*
IN2-40	ZIN2-40	40	80	76	150	125	96,05 €	67,23 €
IN2-60	ZIN2-60	60	120	116	175	150	149,65 €	104,75 €
IN2-80	ZIN2-80	80	160	156	220	200	196,94 €	137,86 €
IN2-100	ZIN2-100	100	200	196	250	220	253,33 €	177,33 €
↓	↓	Gears available up to this size					↓	↓
IN2-110	**ZIN2-110**	**110**	**220**	**216**	**280**	**250**	295,14 €	206,60 €

Dimensions in mm

Our other products


UGH40

H Type Guide units, For Ø40 actuators


HTD5M_09

HTD Heavy duty timing pulley, HTD5 Steel or aluminium


SER69K

Quarter turn latch for the food industry, Stainless steel


MHPGR

Arm with folding rotating handle,


PPG


Indexing plunger with flange, With horizontal mounting flange


EFTC

Fixing support, Stainless steel


ERC

Quick fitting cable terminal, Eye version


B

Steel bevel gear, 1:1


SVR30


Screwjack with travelling nut, with moving nut


PDD

Actuating plunger, Non-rotating detector shaft


UTKpwcr

Utilitrak® 3 wheels carriage, Polymer roller carriage


RPPM

RPP type belt per metre, RPP14 Steel cored polyurethane

Complementary products


IN2

Internal gear, Steel 20NCD2


ZG2

Plastic spur gear, Machined plastic (delrin)


CLG2

Moulded plastic spur gear, Moulded plastic (nylon)