

Steel or **machined** plastic

MODULE
2.0



- Pressure angle 20°
- Materials:
steel 34C10 or
delrin plastic (machined parts)

Options

- Alternative number of teeth
- Alternative materials (stainless steel, brass..)

Accessories

- Spur gears with the same module eg G2., ZG2..




IN: Steel



ZIN: Plastic

NEW!



STEEL DISCOUNTS

Qty.	1+	6+	20+	40+
Disc.	List -12%	-25%	On request	

PLASTIC DISCOUNTS

Qty.	1+	6+	30+
Disc.	List -22%	On request	

STEEL IN	PLASTIC ZIN	Z Teeth	PCD ØP	Part number Internal ØA	ØD	Boss ØM	Price each 1 to 5	STEEL IN	PLASTIC ZIN
IN2-40	ZIN2-40	40	80	76	150	125	96,05 €	67,23 €	
IN2-60	ZIN2-60	60	120	116	175	150	149,65 €	104,75 €	
IN2-80	ZIN2-80	80	160	156	220	200	196,94 €	137,86 €	
IN2-100	ZIN2-100	100	200	196	250	220	253,33 €	177,33 €	
Gears available up to this size									
IN2-110	ZIN2-110	110	220	216	280	250	295,14 €	206,60 €	

Dimensions in mm

Our other products



EMS

Stainless steel knurled thumb nut, Knurled



BCFH

Mushroom headed button Hygienic Usit®, With male thread and high head



PM4

Wormwheel, Bronze



STU

Stroke rotary bushing, Steel



SVG

Adjustable latch clamp with strike plate, Stroke from 118mm to 130,5mm



PGMT

Pull handle, Stainless steel




CDP

Flanged drill bushing, Steel



CHA225

Screwed hinge with threaded insert, 225 degrees



LAT4

4A motorised linear actuator, 4 amperes



HLU

Spoked handwheel without handle, Aluminium



ALIDR30

12 and 24V DC power supplies, 1,5 A and 2 A



T10courroie

T type timing belt, T10 Steel cored polyurethane

Complementary products



IN2

Internal gear, Steel 20NC2



ZG2

Plastic spur gear, Machined plastic (delrin)



CLG2

Moulded plastic spur gear, Moulded plastic (nylon)