


Insertion tool for self tapping inserts

Assembly tool

INSTOOL

- Insertion tool for self tapping inserts
- Hexagonal shaft and rotating hexagonal end



Example of a typical application

DISCOUNTS

Qty	1+	10+	20+	30+	40+
Disc.	List	-5%	-10%	-15%	On request

Part number	Ød	SW	Stock*	Price each 1 to 9
INS300-TOOL-M3	M3	10	✓	89,30 €
INS300-TOOL-M4	M4	10	✓	89,30 €
INS300-TOOL-M5	M5	17	✓	101,20 €
INS300-TOOL-M6	M6	17	✓	101,20 €
INS300-TOOL-M8	M8	17	✓	116,11 €
INS300-TOOL-M10	M10	19	✓	122,06 €
INS300-TOOL-M12	M12	19	✓	157,79 €

*Depending on availability - Dimensions in mm

Fax: 0 825 88 6000 > Service 0,15€/mln + prix appel

cial2@hpceurope.com


WEB
04/2020

HPC


Our other products



PSG15
Spur gear - precision range, Stainless steel 316



PRZ
Wear strip for slat top chain, Z profile to be filled



PTR
Idler chain sprocket, For standard applications



M0
Worm and wheel set, Bronze



H02
Single needle roller universal joint, Heavy duty



BAP
Plastic clamping collar, $\varnothing 10 - \varnothing 20$



PRF-SCREEN-4
Screen support, Support with 4 axes of rotation



BABtss
303 Stainless steel ball pin, 303 Stainless steel



BIMSS
Indexing plunger mini, miniature - Stainless



HRV
V-rail guidance Simple Select®



PFC
Fixed rubber levelling foot, Levelling support



BOX-CS
Hose clamp, Box set of steel hose clamps

Complementary products



INS
Self tapping steel insert, Steel



INS_BR
Self tapping brass insert, Brass



INS_SS
Self tapping stainless steel insert, Stainless steel



INS100
Self tapping inserts-coarse thread, Coarse thread