

- **Stainless steel range**
- Smooth and bushes
- Suitable for speeds up to 800 rpm
- Max. angle of misalignment 90°
- Material:
Stainless steel X5CrNi1810




Uses

- Food and pharmaceutical industries

Accessories

- Optional rubber cover

Modifiable bore



Angle	Factor
5°	1,25
10°	1,00
20°	0,75
30°	0,45
40°	0,30

Effect of operating angle

The torques below are given for a 10° angle. For other angles, the appropriate factor from this table should be applied. E.g. For 10Nm to be transmitted at 20°, the corrected value of torque becomes $10/0.75 = 13.3$ Nm and a joint should be chosen that can transmit 13.3Nm at the required speed.

DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-6%	On request

Part number	ØD	ØA	C	M	L	Torque (Nm)								Stock*	Price each
						at 100 rpm	at 200 rpm	at 300 rpm	at 400 rpm	at 500 rpm	at 700 rpm	at 800 rpm			
JCD04/SS	22	12	25	29	105	18,4	12,4	10,5	9,6	8,7	7,8	5,2	✓	68,04 €	
JCD05/SS	25	14	29	33	119	31,5	18,9	15	12	10,9	9,4	8,7	✓	70,68 €	
JCD06/SS	29	16	30	35	125	49,5	31,9	28,9	26,4	24,4	19,9	18,9	✓	73,56 €	
JCD07/SS	32	18	30	39	134	67,5	63	52,9	42	37,9	30	25,9	-	87,14 €	
JCD08/SS	40	20	32	46	154	175,5	126	87,9	69,9	61,9	43,9	-	✓	95,27 €	
JCD09/SS	40	22	38	46	173	175,5	126	87,9	69,9	61,9	43,9	-	-	119,74 €	
JCD10/SS	50	25	44	59	199	288	180	126	108	90	72	-	-	141,65 €	
JCD11/SS	58	30	58	66	244	324	198	144	117	99	-	-	-	185,76 €	

*Depending on availability - Dimensions in mm

Our other products



MDPOT

Potentiometer,



712_001

Threaded spherical knob, spherical



M2

Worm, Unhardened steel



PLMcr

Magnetic stud, With hook



DB_ECO

Bevel gear - Steel C43, 2:1



CAP805

Plate chain, Large range 805



RHTplss

High Temperature Castor, up to 200kg



MSP3815

Masterplate® glueable insert, rectangular with threaded stud



PRES4HR

Manual bench press, Force up to 600kg



BABS

Ball pin, Hardened stainless steel



PITA

Locking bolt, with T handle



RCX-6

Spherical tilt washer - DIN 6319, concave

Complementary products



M

Bellows cover, Standard



H02SS

Universal joint - stainless steel, Needle bearings - single



HDSS

Universal joint - stainless steel, Needle bearings - double