

# 24V dc motorisation kit

## 2 Planetary gears

KITBUH

- The kit comprises :
  - 1 motorised gearbox BUH77
  - 1 servoamplifier NANO DC-1Q-30/3
  - 1 cable NANO DC-RS232
  - 1 power supply 24V 2.1A
  - 1 cable NANODC-RS232
  - 1 power supply 24V 2,1A (please refer to product pages for full technical details)
- Reduced diameter
- Works in Start/Stop mode or in reverse direction

### Application

- Industrial drives

### Advantages

- Complete set of components
- Easy to install



### DISCOUNTS

Qty	1+	6+	10+
Disc.	List	-7%	On request

Part number	Motor used	Max speed (rpm)	Max torque (Nm)	Price each 1 to 9
KIT-BUH-900	BUH77-24-004	900	0,10	352,89 €
KIT-BUH-260	BUH77-24-012	260	0,30	352,89 €
KIT-BUH-140	BUH77-24-022	140	0,55	352,89 €
KIT-BUH-075	BUH77-24-040	75	1,00	352,89 €
KIT-BUH-023	BUH77-24-135	23	1,80	352,89 €
KIT-BUH-014	BUH77-24-250	14	2,00	352,89 €

Dimensions in mm

## Our other products



GP

Spring loaded toggle latch, With padlock-holder



PFC

Fixed rubber levelling foot, Levelling support for small parts



PTA150

Articulated levelling foot, pressed base Ø150, Ø 150



RCX-6

Spherical tilt washer - DIN6319, convex



BPM-Z

Plastic slotted spring plunger with ball tip, Plastic body + plastic...



RJA00\_02

Sealing strip, Clipping



APB\_T

Adjusting rod for clamp - Female, Bored



GFX

Curved tooth coupling, economy range, Steel and polyamide



RLR

Roll-Ring® chain tensioner, Roll-Ring®



CDP

Flanged drill bushing, Steel



LVT

Miniature motorised actuator 1A, 1 ampere



FGWA

End support, With base

## Complementary products



KITdog

24V DC motorisation kit, Worm and wheel



NANO

Speed controller 3A, 3 A