

24V dc motorisation kit

2 Planetary gears

KITBUH

- The kit comprises :
 - 1 motorised gearbox BUH77
 - 1 servoamplifier NANO DC-1Q-30/3
 - 1 cable NANO DC-RS232
 - 1 power supply 24V 2.1A
 - 1 cable NANODC-RS232
 - 1 power supply 24V 2,1A (please refer to product pages for full technical details)
- Reduced diameter
- Works in Start/Stop mode or in reverse direction

Application

- Industrial drives

Advantages

- Complete set of components
- Easy to install



DISCOUNTS

Qty	1+	6+	10+
Disc.	List	-7%	On request

Part number	Motor used	Max speed (rpm)	Max torque (Nm)	Price each 1 to 9
KIT-BUH-900	BUH77-24-004	900	0,10	352,89 €
KIT-BUH-260	BUH77-24-012	260	0,30	352,89 €
KIT-BUH-140	BUH77-24-022	140	0,55	352,89 €
KIT-BUH-075	BUH77-24-040	75	1,00	352,89 €
KIT-BUH-023	BUH77-24-135	23	1,80	352,89 €
KIT-BUH-014	BUH77-24-250	14	2,00	352,89 €

Dimensions in mm

Our other products



ZBconique
Machined plastic
bevel gear , 1:1



BAG-MI
Split shaft collar with
clamp lever, Steel



CHAC4040NP
Square hinge with
riveted pin, not
drilled, Square with
riveted pin,...



PW_PWG1
Worm - precision
range, Steel



CHB
Double output shaft,
For CHB gearbox



KB_UU
Closed linear
precision bearing,
Precision - steel



VLBS
Folding lifting ring for
welding, Folding - for
welding



PITA
Locking bolt, with T
handle



WJUM20
Drylin® W bearing
block, Slide



CHML40
Worm and wheel gear
reducer, up to 57 Nm
- Integrated torque
limiter




RBG
Wheel, Grey rubber -
Polypropylene rim



DER90
Stainless steel AC
asynchronous motor
1.1 - 1.5kW, 1.1 to
1.5kW

Complementary products



KITdog
24V DC motorisation
kit, Worm and wheel



NANO
Speed controller 3A, 3
A