

24V dc motorisation kit

KITDOG

Worm and wheel

- The kit comprises:
 - 1 motorised gearbox DOG319
 - 1 servoamplifier FIRSTDC-1Q
 - 1 potentiometer MDPOT-10T/10K
 - 1 power supply ALIDR120-2(please refer to product pages for full technical details)
- Reduced size
- Low noise
- Solid design
- Powerful



Application

- Industrial drives

Advantages

- Complete set
- Easy to set up

DISCOUNTS

Qty	1+	6+	10+
Disc. List	-7%	On request	

Part number	Motor used	Max speed (rpm)	Max torque (Nm)	Price each 1 to 9
KIT-DOG-30	DOG319-24-30	30	9	537,41 €
KIT-DOG-45	DOG319-24-45	45	9	537,41 €
KIT-DOG-85	DOG319-24-85	85	4	537,41 €

Dimensions in mm

Our other products



NSU

Universal 90° support clamp, Universal 90° support clamp



PCS50K

Chain sprocket with hardened teeth, 12.7mm (DIN08B-1)



PDM_PDV

Detectable plastic palm grip, blue thermoplastic



RPCplss

Swivel castor with double brake, Stainless steel - Polyamide



BOX-TOR-DRING

Box set of Nitrile D-rings NBR90Sh A, Flange seals



PLM-SC

Magnetic stud with central countersunk hole, With milled bore



CAP805

Slat top chain stainless steel, Large range 805



YG3

HEAVY DUTY spur gear, Steel 35NCD6



VRSSss

Male swivelling lifting rings stainless steel, Male swivelling - s...



H0

Crossed helical gear crossed axis at 90°, Steel 20NCD2



KSM

Cylindrical steel nut, Steel - 1 thread



ETP

Modular handle for aluminium profile, Modular handle

Complementary products



KITbuh

24V DC motorisation kit, Planetary gears



DOG319

Motor-gearbox 12V and 24V DC, from 4 to 9 Nm