


Steel C45 or Stainless steel 316
**KS
KSs**

- Long key bars to be cut to the desired length
- Conform to DIN6880
Material
Steel C45 (Breaking strength 50kg/mm² mini)
Stainless steel 316Ti (X6CrNiMoTi17-12-2)


DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-15%	On request

Part number	Steel		W (h9)	H (h11)	L (mm)	Stock* Steel	Stock* Stainless	Price each 1 to 5	
	Steel	Stainless						Steel	Stainless
KS2-500	-	-	2	2	500	✓	-	5,92 €	-
KS3-500	-	-	3	3	500	✓	-	5,10 €	-
KS4-500	-	-	4	4	500	✓	-	6,12 €	-
KS5-500	-	KS5-500/SS	5	5	500	✓	✓	7,86 €	57,97 €
KS6-500	-	KS6-500/SS	6	6	500	✓	-	10,05 €	59,75 €
KS8-500	-	-	8	8	500	✓	-	11,67 €	-
KS87-500	-	KS87-500/SS	8	7	500	✓	-	10,04 €	84,71 €
KS10-500	-	-	10	10	500	✓	-	17,06 €	-
KS108-500	-	KS108-500/SS	10	8	500	✓	-	14,28 €	118,32 €
KS12-500	-	-	12	12	500	-	-	22,37 €	-
KS128-500	-	KS128-500/SS	12	8	500	✓	-	12,83 €	142,40 €
KS14-500	-	-	14	14	500	-	-	26,41 €	-
KS149-500	-	KS149-500/SS	14	9	500	✓	-	16,84 €	193,80 €
KS1610-500	-	KS1610-500/SS	16	10	500	✓	-	21,36 €	240,16 €
KS1811-500	-	KS1811-500/SS	18	11	500	✓	-	26,44 €	287,13 €
KS2012-500	-	-	20	12	500	✓	-	30,05 €	-
KS2214-500	-	KS2214-500/SS	22	14	500	-	-	38,96 €	431,90 €
KS2514-500	-	-	25	14	500	✓	-	44,22 €	-

*Depending on availability - Dimensions in mm