

## Steel C45 or Stainless steel 316

### KS KSss

- Long key bars to be cut to the desired length

- Conform to DIN6880


Material

Steel C45 (Breaking strength

50kg/mm<sup>2</sup> mini)

Stainless steel 316Ti

(X6CrNiMoTi17-12-2)



### DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-15%	On request

Part number	W	H	L	Stock*		Price each 1 to 5		
				Steel	Stainless	Steel	Stainless	
Steel	Stainless	(h9)	(h11)	(mm)				
KS2-500	-	2	2	500	-	-	5,80 €	-
KS3-500	-	3	3	500	-	-	5,00 €	-
KS4-500	-	4	4	500	-	-	6,00 €	-
KS5-500	KS5-500/SS	5	5	500	-	-	7,70 €	56,84 €
KS6-500	KS6-500/SS	6	6	500	-	-	9,85 €	58,58 €
KS8-500	-	8	8	500	-	-	11,44 €	-
KS87-500	KS87-500/SS	8	7	500	-	-	9,84 €	83,04 €
KS10-500	-	10	10	500	-	-	16,72 €	-
KS108-500	KS108-500/SS	10	8	500	-	-	14,00 €	115,99 €
KS12-500	-	12	12	500	-	-	21,93 €	-
KS128-500	KS128-500/SS	12	8	500	-	-	12,57 €	139,59 €
KS14-500	-	14	14	500	-	-	25,89 €	-
KS149-500	KS149-500/SS	14	9	500	-	-	16,50 €	189,98 €
KS1610-500	KS1610-500/SS	16	10	500	-	-	20,94 €	235,43 €
KS1811-500	KS1811-500/SS	18	11	500	-	-	25,92 €	281,48 €
KS2012-500	-	20	12	500	-	-	29,46 €	-
KS2214-500	KS2214-500/SS	22	14	500	-	-	38,19 €	423,38 €
KS2514-500	-	25	14	500	-	-	43,35 €	-

\*Depending on availability - Dimensions in mm

## Our other products



HW\_HT  
Half-rail guide, Wheel



DER71  
Stainless steel AC asynchronous motor  
0.25 à 0.37kW, 0.25 to 0.37kW



RFK48C  
Hypoid gearbox -  
Stainless steel, up to  
350 Nm



EHD12  
Internal epicyclic  
servo reducers, from  
60 to 140 Nm



PTAF80-PAMF80  
Articulated fixable  
foot with pressed  
base Ø80, Ø 80



BAG0  
Locking rings in steel,  
Steel



MEFC  
Flanged sintered  
ferrous bush, Self-  
lubricating FP20  
ferrous alloy M...



ZG125  
Plastic spur gear,  
Machined plastic  
(delrin)



DHX  
Dowel pin internal  
thread, Extractable  
DIN 7979D



NT91  
Spur gear coaxial  
gearbox, from 10 to  
35 Nm - Inline



PRF\_CHA  
Hinge for aluminium  
profile, Surface  
mounting hinge




GARDLL  
Mounting sleeve for  
lock pin, Nickel-plated  
steel or Stainless steel

## Complementary products



KK  
Rounded end feather  
key, Steel



KS  
Keysteel, Stainless  
steel - Keystock