


## Steel or 316 stainless steel

### KS KSss

- To be cut to desired length
- Conforms to BS 4235 Part 1 1967
- Materials:  
Steel C45  
Stainless steel 316



### DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-15%	-20%	On request

Part number		W (h9)	H (h11)	L (mm)	Stock*	Stock*	Price each 1 to 5	
Steel	Stainless				Steel	Stainless	Steel	Stainless
KS-2	-	2	2	300	✓	-	2,87 €	-
KS-3	-	3	3	300	✓	-	2,87 €	-
KS-4	-	4	4	300	✓	-	3,33 €	-
KS-5	KS-5SS	5	5	300	✓	✓	4,34 €	11,59 €
KS-6	KS-6SS	6	6	300	✓	✓	4,78 €	14,68 €
KS-8	-	8	8	300	✓	-	3,91 €	-
KS-87	KS-87SS	8	7	300	✓	✓	3,91 €	31,29 €
KS-10	-	10	10	300	✓	-	5,24 €	-
KS-108	KS-108SS	10	8	300	✓	✓	4,78 €	50,07 €
KS-12	-	12	12	300	✓	-	7,33 €	-
KS-128	KS-128SS	12	8	300	✓	✓	5,78 €	59,55 €
KS-14	-	14	14	300	✓	-	8,19 €	-
KS-149	KS-149SS	14	9	300	✓	-	7,74 €	58,17 €
KS-1610	KS-1610SS	16	10	300	✓	-	7,74 €	82,67 €
KS-1811	KS-1811SS	18	11	300	✓	-	8,76 €	69,32 €
KS-2012	-	20	12	300	✓	-	11,73 €	-
KS-2214	KS-2214SS	22	14	300	✓	-	14,14 €	128,69 €
KS-2514	-	25	14	300	✓	-	14,67 €	-

\*Depending on availability - Dimensions in mm

## Our other products



RBN

Wheel, Rubber tyre -  
Polypropylene rim



DIA

Ring operated locking  
bolt, with ring



MDB\_MTB

Moulded plastic bevel  
gear (nylon), 3:1



AF

Shaft clamp with  
keyway, Set screw



G2

Steel spur gear, Steel  
20NCD2



HLU

Spoked handwheel  
without handle,  
Aluminium



LACM\_SS

Stainless steel cam  
lever, Female




RCC\_RCX

Spherical tilt washer -  
DIN6319, convex



SLHHlok

Horizontal toggle  
clamp, Horizontal  
toggle clamp /



RPPM

RPP type belt per  
metre, RPP14 Steel  
cored polyurethane



PM3

Worm and wheel set,  
Non hardened steel



RPP


Connecting plate for  
RPP type timing belts,  
RPP8

## Complementary products



KK

Rounded end feather  
key, Steel



KS

Keysteel, Stainless  
steel - Keystock