


## KSM 1 trapezoidal right or left-hand thread KSM<sub>LH</sub>

- Right or left-hand thread
- Thread conforms to NFE 03.616
- Machined nut
- Thread tolerance: 7H
- Material: Steel 11SMnPb37



### Accessories

- LFM steel leadscrew or LSM stainless steel leadscrew

### DISCOUNTS <sup>Ⓐ</sup>

Qty	1+	10+	20+	40+
Disc.	List	-30%	-40%	On request

### DISCOUNTS <sup>Ⓑ</sup>

Qty	1+	5+	10+
Disc.	List	-5%	On request

Part number	Ød	Pitch P	D	C	Weight (kg)	Stock*	Price each	
							1 to 9	20 to 39**
<b>Right-hand thread</b>								
KSM102	10	2	22	15	0,035	✓	Ⓐ 3,76 €	Ⓐ 2,25 €
KSM123	12	3	26	18	0,055	✓	Ⓐ 4,07 €	Ⓐ 2,45 €
KSM143	14	3	30	21	0,090	✓	Ⓐ 5,09 €	Ⓐ 3,06 €
KSM164	16	4	36	24	0,155	✓	Ⓐ 6,67 €	Ⓐ 4,00 €
KSM184	18	4	40	27	0,215	✓	Ⓐ 7,57 €	Ⓐ 4,55 €
KSM204	20	4	45	30	0,305	✓	Ⓐ 9,47 €	Ⓐ 5,68 €
KSM225	22	5	45	33	0,322	✓	Ⓐ 10,25 €	Ⓐ 6,15 €
KSM245	24	5	50	36	0,440	✓	Ⓐ 12,04 €	Ⓐ 7,23 €
KSM285	28	5	60	42	0,740	✓	Ⓐ 18,99 €	Ⓐ 11,40 €
KSM306	30	6	60	45	0,765	✓	Ⓐ 19,84 €	Ⓐ 11,91 €
KSM326	32	6	60	48	0,790	-	Ⓐ 20,75 €	Ⓐ 12,44 €
KSM366	36	6	75	54	1,470	-	Ⓑ 25,67 €	Ⓑ On request
KSM407	40	7	80	60	1,830	✓	Ⓑ 30,76 €	Ⓑ On request
KSM447	44	7	80	66	1,890	-	Ⓑ 40,41 €	Ⓑ On request
KSM508	50	8	90	75	2,695	-	Ⓑ 86,91 €	Ⓑ On request
KSM609	60	9	100	90	3,865	-	Ⓑ 107,84 €	Ⓑ On request
KSM7010	70	10	110	100	5,115	-	Ⓑ 133,58 €	Ⓑ On request
KSM8010	80	10	120	110	6,000	-	Ⓑ 173,83 €	Ⓑ On request
<b>Left-hand thread</b>								
KSM102/LH	10	2	22	15	0,035	-	Ⓐ 7,53 €	Ⓐ 4,52 €
KSM123/LH	12	3	26	18	0,055	✓	Ⓐ 6,64 €	Ⓐ 3,98 €
KSM143/LH	14	3	30	21	0,090	✓	Ⓐ 11,42 €	Ⓐ 6,85 €
KSM164/LH	16	4	36	24	0,155	✓	Ⓐ 9,20 €	Ⓐ 5,52 €
KSM184/LH	18	4	40	27	0,215	-	Ⓐ 8,45 €	Ⓐ 5,08 €
KSM204/LH	20	4	45	30	0,305	✓	Ⓐ 10,32 €	Ⓐ 6,19 €
KSM225/LH	22	5	45	33	0,322	-	Ⓐ 16,64 €	Ⓐ 9,98 €
KSM245/LH	24	5	50	36	0,440	-	Ⓐ 15,80 €	Ⓐ 9,48 €
KSM285/LH	28	5	60	42	0,740	✓	Ⓐ 25,10 €	Ⓐ 15,06 €
KSM306/LH	30	6	60	45	0,765	-	Ⓐ 24,44 €	Ⓐ 14,67 €
KSM326/LH	32	6	60	48	0,790	-	Ⓐ 27,36 €	Ⓐ 16,42 €
KSM366/LH	36	6	75	54	1,470	-	Ⓑ 28,14 €	Ⓑ On request
KSM407/LH	40	7	80	60	1,830	-	Ⓑ 34,91 €	Ⓑ On request
KSM447/LH	44	7	80	66	1,890	-	Ⓑ 46,86 €	Ⓑ On request
KSM508/LH	50	8	90	75	2,695	-	Ⓑ 154,95 €	Ⓑ On request
KSM609/LH	60	9	100	90	3,865	-	Ⓑ 175,81 €	Ⓑ On request
KSM7010/LH	70	10	110	100	5,115	-	Ⓑ 201,50 €	Ⓑ On request
KSM8010/LH	80	10	120	100	6,000	-	Ⓑ 230,23 €	Ⓑ On request

\*Depending on availability - Dimensions in mm

\*\* refer to discounts

## Our other products



RTTss

Locking assembly,  
Medium/high torque



MEB

Moulded plastic bevel  
gear (nylon), 1:1



MDB\_MTB

Moulded plastic bevel  
gear (nylon), 2:1



MAC

Carabiner DIN5299  
steel, Steel



DER80

Stainless steel AC  
asynchronous motor  
0.55 - 0.75kW, 0.55 to  
0.75kW



CHM63-MOT

Asynchronous AC  
motorgearboxes 0.37  
to 1.5kW, 0.37 to  
1.5kW



PPRss

Pad eye on mounting  
plate round, Stainless  
steel



MEB

Moulded plastic bevel  
gear (nylon), 1:1



PM3

Worm and wheel set,  
Bronze



BPFL

Sheet steel flanged  
bearing for light  
loads, Sheet steel



GLT3-76

Telescopic drawer,



NSP

Right angled support  
clamp, Right angled  
support clamp

## Complementary products



LFM

Steel leadscrew,  
Medium carbon steel -  
1 thread




LSM

Stainless steel 316L  
leadscrew, Stainless  
steel - 1 thread



LFM

Steel leadscrew,  
Medium carbon steel -  
1 thread



LSM

Stainless steel 316L  
leadscrew, Stainless  
steel - 1 thread