

- Cold rolled (plastic deformation)
- Conforms to DIN 103 (NFE 03-615)
- Capable of transmitting large forces
- Good surface finish
- Material: Half-hard steel XC38
- Thread tolerance: 7e

Uses




- Machine tools
- Lathe main screw

Accessories

- LRM and BFM dual thread bronze nuts
- KSM dual thread steel nuts

Options

- Available in lengths up to 6000mm (subject to diameter)



DISCOUNTS and AVAILABLE LENGTHS

Qty	1+	10+	20+	40+
Disc.	List	-30%	-40%	On request
Long	1000	2000	3000	6000 mm
Price	Each	x2,12	x3,18	On request

Part number	ØD	Pitch P (mm)	d min.	Price per metre	
				1 to 9	20 to 39**
LFM126	12	6	07,68	12,82 €	7.69
LFM146	14	6	09,68	16,42 €	9.85
LFM168	16	8	10,47	21,46 €	12.88
LFM188	18	8	12,47	30,20 €	18.12
LFM208	20	8	14,47	32,85 €	19.71
LFM2210	22	10	15,29	38,42 €	23.05
LFM2410	24	10	17,27	43,37 €	26.02
LFM2610	26	10	19,27	63,58 €	38.15
LFM2810	28	10	21,27	71,58 €	42.95
LFM3012	30	12	21,56	60,28 €	36.17
LFM3212	32	12	23,56	98,58 €	59.15
LFM3612	36	12	27,56	97,93 €	58.76
LFM4014	40	14	30,38	121,49 €	72.89

Dimensions in mm

** REFER TO DISCOUNTS

Our other products



PRF_FIX_ANG

Fastener for aluminium profile, Angular joint



ALIDR30

12 and 24V DC power supplies, 1,5 A and 2 A



CHA60

Rectangular hinge, drilled or countersunk, Rectangular, drilled or C...



GBMf

Flanged leadscrew nut, Flanged nut - Multiple starts



PRF_CHA_D

Hinge and joint, Lift-off hinge



BOX-NINA

Self locking nut - DIN985, Box set of steel nuts



BCM_MPBT

Modular cylindrical brush, PBT polyester bristles



BLHB50

Right angled gearbox, bored shafts, up to 30 Nm




DILC

Indexing plunger with cam, with cam



PRF1932

Standard aluminium profile, 19 x 32 mm



AC

Strike for toggle latch, 15mm



ACLLPP

Latch for aluminium profile, Spring operated latch

Complementary products



BFM2

Flanged bronze nut, Bronze - 2 threads



LRM2

Cylindrical bronze nut, Bronze - 2 threads