Spring loaded latch

LRR


Plated steel


- **Spring return latch**
- Inward/outward opening versions available (A+ B versions)
- Materials :
  Galvanised steel


Accessory


- Catch plate **LRRGPV** **(tome 5 p.197)**











DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	List	-3%	-5%	On request

Part number	A	B	C	D	E	F	G	H	J	K	ØS	Material	Weight (g)	Stock*	Price each 1 to 9
Version A															
LRR-50-A/ZN	50	56	1,5	1,2	16	20	34	27	12	12	4	Steel	71	✔	22,27 €
Version B															
LRR-50-B/ZN	50	56	1,5	1,2	16	20	34	27	12	12	4	Steel	71	✔	22,27 €

**Depending on availability - Dimensions in mm*

Stock Catch-plate for spring loaded latch


Plated steel


LRRGPV

- ***Catch for sprung latch LRR***
- *Materials :*
  Galvanised steel

Accessory

- *Spring loaded latch* **LRR** *(tome 5 p.196)*





DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	List	-3%	-5%	On request

Part number	A	B	C	D	G	H	ØS	Material	Weight (g)	Stock*	Price each 1 to 9
LRR-50-GPV/ZN	50	16	1,5	16	34	16	4	Steel	12	✔	3,26 €

**Depending on availability - Dimensions in mm*

Slam latches

LRRSS

Stainless steel

- ***Slam latches for direct closing in hostile environments***
- *Latch tongue at top*
- *Resistant to water and cleaning products*
- *Materials:*
  Body and support: 304L stainless steel
  Latch and handle: 303 stainless steel
  Spring: 301 stainless steel





Advantages


- *Openings on the top and mounting face allow easy cleaning (no retention of water or dirt)*
- *No sharp angles (avoids risk of injury)*
- *Top mounted handle allows easy opening*


Applications


- *Equipment for the food industry*
- *Animal breeding (hutches, hen-houses)*
- *Lids for metal enclosures used in humid environments*
- *Stainless steel strike plate not supplied*















A version



B version

DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	List	-3%	-5%	On request

Part number	Latch stroke (mm)	Type	Stock*	Price each 1 to 9
LRR-56-A/SS	12	A version	✔	30,53 €
LRR-56-B/SS	13	B version	✔	41,68 €

*Dimensions in mm. *Depending on availability*

Spring return latch


Steel or stainless steel


LRR


- ***Spring loaded single bolt***
- *Rolled knot hinge*
- *Material:*
  White galvanized steel
  Stainless steel 304

Advantages


- *Simple locking*
- *Retractable pivot*







Right handed



Left handed

DISCOUNTS

Qty	1+	50+	100+
Disc.	Net	-10%	On request

Part number	Version	Stock*	Price each 1 to 49
Steel version			
LRR-53-26/D	Right	✔	3,25 €
LRR-53-26/G	Left	-	3,25 €
Stainless steel version			
LRR-53-26/G/SS	Left	✔	6,51 €
LRR-53-26/D/SS	Right	✔	6,51 €

**Depending on availability - Dimensions in mm*

Small dimension latch with locking system Alu


LRR22

In aluminium


- ***Springloaded bolt can be held in unlocked position***
- *Materials:*
  Body: aluminium 6060T5 clear anodised
  Shaft and handle: raw aluminium
  Cap: Black PE
  Spring: Stainless steel
  Strike: aluminium 5754 clear anodised

Note


There is no strike for this size




Springloaded bolt



Type 2
LRR-22-2/ALU



Type 1
LRR-22-1/ALU



DISCOUNT

Qty	1+	10+	20+	50+
Disc.	List	-3%	-5%	On request

Part number	A	B	C	Type	Weight (g)	Price each 1 to 9
Springloaded bolt						
LRR-22-2/ALU	30	22,5	18,2	2	9	17,19 €
LRR-22-1/ALU	30	22,5	18,2	1	9	17,19 €


Dimensions in mm

Latch with locking system


In aluminium

LRR37


- ***Springloaded bolt can be held in unlocked position***
- *It is recommended to combine 1 latch with 1 strike*
- *Materials:*
  - *Body: aluminium 6060T5 clear anodised*
  - *Shaft and handle: raw aluminium*
  - *Cap: Black PE*
  - *Spring: Stainless steel*
  - *Strike: aluminium 5754 clear anodised*




Springloaded bolt




Strike




Type 2
LRR-37-2/ALU



Type 1
LRR-37-1/ALU





LRR-37-GPV/ALU

DISCOUNT

Qty	1+	10+	20+	50+
Disc.	List	-3%	-5%	On request

Part number	A	B	C	Type	Weight (g)	Price each 1 to 9
Springloaded bolt						
LRR-37-2/ALU	60	36,5	34	2	58	28,02 €
LRR-37-1/ALU	60	36,5	34	1	58	28,02 €
Strike						
LRR-37-GPV/ALU	25	37	19	-	11	4,96 €


Dimensions in mm


Ball catch


LQT

with 2 balls

- ***Quick closing catch***
- *Push to close*
- *Material:*
  Chromed die cast zinc







DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	A	B	C	C1	C2	D	E	F	G
LQT-2B-42-8	42,5	8,0	14,0	10,0	6,5	26,7	2,5	35	16
LQT-2B-50-10	50,0	10,0	16,0	12,5	7,4	29,8	3,0	40	20
LQT-2B-70-13	70,0	13,5	21,2	17,0	11,0	49,0	4,0	60	30

Part number	H	J	K	L	S1	S2	Force (N)	Weight (g)	Stock*	Price each 1 to 5
LQT-2B-42-8	25	7,5	11,3	2,5	3,2	3,2	30	16	✔	13,80 €
LQT-2B-50-10	30	9,0	12,3	2,5	4,2	4,2	33	26	✔	16,24 €
LQT-2B-70-13	42	10,5	17,2	3	4,2	4,2	35	70	✔	28,00 €

**Depending on availability - Dimensions in mm*