


- Type C Carabiner
- White zinc plated steel
- Product carries no certification marking

Application

- The breaking strength is obtained by multiplying the SWL by a factor of safety of 4

Info

- Not suitable for climbing
- Also exists in stainless steel



DISCOUNTS

Qty	1+	20+	40+	60+	80+	100+
Disc.	List	-5%	-10%	-15%	-20%	On request

Part number	ØD	L	A	C	SWL (kg)	Weight (g)	Stock*	Price each 1 to 19
MAC5-50	5	50	8	7	50	16	✓	1,44 €
MAC6-60	6	60	8	8	90	26	✓	1,64 €
MAC7-70	7	70	11	9	150	44	✓	2,22 €
MAC8-80	8	80	12	10	190	62	✓	2,25 €
MAC9-90	9	90	13	11	230	92	-	2,47 €
MAC10-100	10	100	16	13	310	126	-	3,01 €
MAC11-120	11	120	19	17	340	192	-	3,92 €
MAC12-140	12	140	20	19	380	256	-	5,32 €

*Depending on availability - Dimensions in mm


- Type C Carabiner
- Stainless steel 316
- Product carries no certification marking

Application

- The breaking strength is obtained by multiplying the SWL by a factor of safety of 4

Info

- Not suitable for climbing
- Also exists in steel



DISCOUNTS

Qty	1+	20+	40+	60+	80+	100+
Disc.	List	-5%	-10%	-15%	-20%	On request

Part number	D	L	A	C	SWL (kg)	Weight (g)	Stock*	Price each 1 to 19
MAC5-50/SS	5	50	8	7	90	16	✓	3,73 €
MAC6-60/SS	6	60	8	8	150	28	✓	4,46 €
MAC7-70/SS	7	70	10	9	180	43	✓	6,30 €
MAC8-80/SS	8	80	12	11	225	66	✓	7,15 €
MAC10-100/SS	10	100	14	14	375	129	✓	10,20 €
MAC11-120/SS	11	120	19	17	390	186	-	13,40 €
MAC12-140/SS	12	140	23	21	410	260	-	18,50 €

*Depending on availability - Dimensions in mm