


- Cylindrical sleeves, through threaded
- Suitable for joining threaded bars
- Materials:
Zn3-5BL galvanised steel S300PB
Stainless steel 303
- Sold by the packet

Steel or stainless steel



DISCOUNTS

No. packets	1+	5+	20+	50+
Discounts	List	-5%	-10%	On request

Part number		Thread	ØT	L	ØD	Qty per packet	Stock*		Price per packet 1 to 4	
Steel	Stainless steel						Steel	S/steel	Steel	S/steel
MCL4-15/B	-	M4	15	7	20	✓	-	4,55 €	-	
MCL4-20/B	-	M4	20	7	20	✓	-	4,83 €	-	
-	MCL5-15/SS/B	M5	15	8	20	-	✓	-	23,87 €	
MCL5-20/B	-	M5	20	8	20	✓	-	4,93 €	-	
MCL5-25/B	-	M5	25	8	20	✓	-	5,31 €	-	
MCL6-10/B	MCL6-10/SS/B	M6	10	10	20	✓	✓	4,15 €	20,60 €	
MCL6-15/B	-	M6	15	10	20	-	-	4,55 €	-	
MCL6-20/B	MCL6-20/SS/B	M6	20	10	20	✓	✓	5,12 €	25,02 €	
MCL6-25/B	MCL6-25/SS/B	M6	25	10	20	✓	✓	5,50 €	30,30 €	
MCL6-30/B	MCL6-30/SS/B	M6	30	10	20	✓	✓	6,27 €	35,40 €	
MCL6-35/B	-	M6	35	10	20	✓	-	7,81 €	-	
MCL6-40/B	-	M6	40	10	20	✓	-	8,30 €	-	
MCL6-50/B	-	M6	50	10	20	✓	-	14,73 €	-	
MCL8-15/B	-	M8	15	11	20	✓	-	5,12 €	-	
MCL8-20/B	MCL8-20/SS/B	M8	20	11	20	-	✓	5,50 €	32,99 €	
MCL8-25/B	MCL8-25/SS/B	M8	25	11	20	✓	-	5,88 €	35,40 €	
MCL8-30/B	MCL8-30/SS/B	M8	30	11	20	✓	✓	6,47 €	43,17 €	
MCL8-35/B	MCL8-35/SS/B	M8	35	11	20	-	-	8,68 €	46,93 €	
MCL8-40/B	MCL8-40/SS/B	M8	40	11	20	✓	-	9,26 €	52,71 €	
MCL8-50/B	MCL8-50/SS/B	M8	50	11	20	✓	✓	14,92 €	65,96 €	
MCL10-20/B	MCL10-20/SS/B	M10	20	13	20	✓	-	6,95 €	41,18 €	
MCL10-25/B	MCL10-25/SS/B	M10	25	13	20	-	✓	8,11 €	51,06 €	
MCL10-30/B	MCL10-30/SS/B	M10	30	13	20	-	-	8,68 €	60,58 €	
MCL10-35/B	-	M10	35	13	20	-	-	10,22 €	-	
MCL10-40/B	MCL10-40/SS/B	M10	40	13	20	-	✓	11,75 €	71,82 €	
MCL10-50/B	MCL10-50/SS/B	M10	50	13	20	-	✓	17,90 €	89,50 €	
MCL10-60/B	-	M10	60	13	20	-	-	21,83 €	-	
MCL12-20/B	-	M12	20	15	20	✓	-	9,84 €	-	
MCL12-25/B	-	M12	25	15	20	-	-	10,81 €	-	
MCL12-30/B	MCL12-30/SS/B	M12	30	15	20	-	✓	12,24 €	80,46 €	
MCL12-35/B	-	M12	35	15	20	-	-	14,34 €	-	
MCL12-40/B	MCL12-40/SS/B	M12	40	15	20	-	-	15,80 €	93,08 €	
MCL12-50/B	MCL12-50/SS/B	M12	50	15	20	-	-	24,26 €	103,92 €	
MCL12-60/B	-	M12	60	15	20	-	-	30,80 €	-	

*Depending of availability - Dimensions in mm

Our other products



M0
Worm and wheel set,
Machined plastic
(delrin)



LFM2
Steel leadscrew,
Medium carbon steel -
2 threads



GG3
Ground spur gear,
Heat treated steel



BPTR_M
End cap with threaded
insert for round tube,
With threaded insert



ZBconique
Machined plastic
bevel gear, 1:1



COA-COG
Surface mounting
plate, Surface
mounting plate for
ball joint



WBGV
Lifting ring, Threaded



HK
Manual locking clamp,
Manual locking clamp
LRX



PRF-SCREEN-5
Screen support,
Support with 5 axes of
rotation



PLM-C
Cylindrical holding
magnets, Cylindrical
holding magnet



BOXKU
Boxed set of half
round (Woodruff) keys
NFE22179, Boxed set



ZG125
Plastic spur gear,
Machined plastic
(delrin)

Complementary products



MCL
Cylindrical threaded
sleeve, Cylindrical -
steel



TIF
Threaded rod -
DIN975, Stainless
steel A2



MHXred
Reducing sleeve
male/female,
Hexagonal - stainless
steel



MCLred
Reducing sleeve
female/female,
Cylindrical - stainless
steel