


- Cylindrical sleeves, through threaded
- Suitable for joining threaded bars
- Materials:
Zn3-5BL galvanised steel S300PB
Stainless steel 303
- Sold by the packet

Steel or stainless steel



DISCOUNTS

No. packets	1+	5+	20+	50+
Discounts	List	-5%	-10%	On request

Part number		Thread	ØT	L	ØD	Qty per packet	Stock*		Price per packet 1 to 4	
Steel	Stainless steel						Steel	S/steel	Steel	S/steel
MCL4-15/B	-	M4	15	7	20	✓	-	4,55 €	-	
MCL4-20/B	-	M4	20	7	20	✓	-	4,83 €	-	
-	MCL5-15/SS/B	M5	15	8	20	-	✓	-	23,87 €	
MCL5-20/B	-	M5	20	8	20	✓	-	4,93 €	-	
MCL5-25/B	-	M5	25	8	20	✓	-	5,31 €	-	
MCL6-10/B	MCL6-10/SS/B	M6	10	10	20	✓	✓	4,15 €	20,60 €	
MCL6-15/B	-	M6	15	10	20	-	-	4,55 €	-	
MCL6-20/B	MCL6-20/SS/B	M6	20	10	20	✓	✓	5,12 €	25,02 €	
MCL6-25/B	MCL6-25/SS/B	M6	25	10	20	✓	✓	5,50 €	30,30 €	
MCL6-30/B	MCL6-30/SS/B	M6	30	10	20	✓	✓	6,27 €	35,40 €	
MCL6-35/B	-	M6	35	10	20	✓	-	7,81 €	-	
MCL6-40/B	-	M6	40	10	20	✓	-	8,30 €	-	
MCL6-50/B	-	M6	50	10	20	✓	-	14,73 €	-	
MCL8-15/B	-	M8	15	11	20	✓	-	5,12 €	-	
MCL8-20/B	MCL8-20/SS/B	M8	20	11	20	-	✓	5,50 €	32,99 €	
MCL8-25/B	MCL8-25/SS/B	M8	25	11	20	✓	-	5,88 €	35,40 €	
MCL8-30/B	MCL8-30/SS/B	M8	30	11	20	✓	✓	6,47 €	43,17 €	
MCL8-35/B	MCL8-35/SS/B	M8	35	11	20	-	-	8,68 €	46,93 €	
MCL8-40/B	MCL8-40/SS/B	M8	40	11	20	✓	-	9,26 €	52,71 €	
MCL8-50/B	MCL8-50/SS/B	M8	50	11	20	✓	✓	14,92 €	65,96 €	
MCL10-20/B	MCL10-20/SS/B	M10	20	13	20	✓	-	6,95 €	41,18 €	
MCL10-25/B	MCL10-25/SS/B	M10	25	13	20	-	✓	8,11 €	51,06 €	
MCL10-30/B	MCL10-30/SS/B	M10	30	13	20	-	-	8,68 €	60,58 €	
MCL10-35/B	-	M10	35	13	20	-	-	10,22 €	-	
MCL10-40/B	MCL10-40/SS/B	M10	40	13	20	-	✓	11,75 €	71,82 €	
MCL10-50/B	MCL10-50/SS/B	M10	50	13	20	-	✓	17,90 €	89,50 €	
MCL10-60/B	-	M10	60	13	20	-	-	21,83 €	-	
MCL12-20/B	-	M12	20	15	20	✓	-	9,84 €	-	
MCL12-25/B	-	M12	25	15	20	-	-	10,81 €	-	
MCL12-30/B	MCL12-30/SS/B	M12	30	15	20	-	✓	12,24 €	80,46 €	
MCL12-35/B	-	M12	35	15	20	-	-	14,34 €	-	
MCL12-40/B	MCL12-40/SS/B	M12	40	15	20	-	-	15,80 €	93,08 €	
MCL12-50/B	MCL12-50/SS/B	M12	50	15	20	-	-	24,26 €	103,92 €	
MCL12-60/B	-	M12	60	15	20	-	-	30,80 €	-	

*Depending of availability - Dimensions in mm

Our other products



SDG
Adjustable guide support bracket, Plastic



M0
Worm and wheel set, Machined plastic (delrin)



AT5courroie
AT type timing belt, AT5 Steel cored polyurethane



CHB
Double output shaft, For CHB gearbox



CHM30-MOT
Asynchronous AC motorgearboxes 0.09 to 0.22kW, 0.09 to 0.22kW



DOMI80
Domino 80 adjustable slide, Slide DOMILINE 80




R203
Die spring ISO10243, Light



SH1
Parallel axis helical gear, Machined plastic (delrin)



H4
Crossed helical gear crossed axis at 90°



RPPM
RPP type belt per metre, RPP14 Steel



PLC_PLT
Magnetic stud with threaded hole, With



BSB
Ball screw bearing unit, Support

Complementary products



MCL
Cylindrical threaded sleeve, Cylindrical - steel



TIF
Threaded rod - DIN975, Stainless steel A2



MHXred
Reducing sleeve male/female, Hexagonal - stainless steel



MCLred
Reducing sleeve female/female, Cylindrical - stainless steel