


- Cylindrical sleeves, through threaded
- Suitable for joining threaded bars
- Materials:
Zn3-5BL galvanised steel S300PB
Stainless steel 303
- Sold by the packet

Steel or stainless steel



DISCOUNTS

No. packets	1+	5+	20+	50+
Discounts	List	-5%	-10%	On request

Part number		Thread	ØT	L	ØD	Qty per packet	Stock*		Price per packet 1 to 4	
Steel	Stainless steel						Steel	S/steel	Steel	S/steel
MCL4-15/B	-	M4	15	7	20	✓	-	4,55 €	-	
MCL4-20/B	-	M4	20	7	20	✓	-	4,83 €	-	
-	MCL5-15/SS/B	M5	15	8	20	-	✓	-	23,87 €	
MCL5-20/B	-	M5	20	8	20	✓	-	4,93 €	-	
MCL5-25/B	-	M5	25	8	20	✓	-	5,31 €	-	
MCL6-10/B	MCL6-10/SS/B	M6	10	10	20	✓	✓	4,15 €	20,60 €	
MCL6-15/B	-	M6	15	10	20	-	-	4,55 €	-	
MCL6-20/B	MCL6-20/SS/B	M6	20	10	20	✓	✓	5,12 €	25,02 €	
MCL6-25/B	MCL6-25/SS/B	M6	25	10	20	✓	✓	5,50 €	30,30 €	
MCL6-30/B	MCL6-30/SS/B	M6	30	10	20	✓	✓	6,27 €	35,40 €	
MCL6-35/B	-	M6	35	10	20	✓	-	7,81 €	-	
MCL6-40/B	-	M6	40	10	20	✓	-	8,30 €	-	
MCL6-50/B	-	M6	50	10	20	✓	-	14,73 €	-	
MCL8-15/B	-	M8	15	11	20	✓	-	5,12 €	-	
MCL8-20/B	MCL8-20/SS/B	M8	20	11	20	-	✓	5,50 €	32,99 €	
MCL8-25/B	MCL8-25/SS/B	M8	25	11	20	✓	-	5,88 €	35,40 €	
MCL8-30/B	MCL8-30/SS/B	M8	30	11	20	✓	✓	6,47 €	43,17 €	
MCL8-35/B	MCL8-35/SS/B	M8	35	11	20	-	-	8,68 €	46,93 €	
MCL8-40/B	MCL8-40/SS/B	M8	40	11	20	✓	-	9,26 €	52,71 €	
MCL8-50/B	MCL8-50/SS/B	M8	50	11	20	✓	✓	14,92 €	65,96 €	
MCL10-20/B	MCL10-20/SS/B	M10	20	13	20	✓	-	6,95 €	41,18 €	
MCL10-25/B	MCL10-25/SS/B	M10	25	13	20	-	✓	8,11 €	51,06 €	
MCL10-30/B	MCL10-30/SS/B	M10	30	13	20	-	-	8,68 €	60,58 €	
MCL10-35/B	-	M10	35	13	20	-	-	10,22 €	-	
MCL10-40/B	MCL10-40/SS/B	M10	40	13	20	-	✓	11,75 €	71,82 €	
MCL10-50/B	MCL10-50/SS/B	M10	50	13	20	-	✓	17,90 €	89,50 €	
MCL10-60/B	-	M10	60	13	20	-	-	21,83 €	-	
MCL12-20/B	-	M12	20	15	20	✓	-	9,84 €	-	
MCL12-25/B	-	M12	25	15	20	-	-	10,81 €	-	
MCL12-30/B	MCL12-30/SS/B	M12	30	15	20	-	✓	12,24 €	80,46 €	
MCL12-35/B	-	M12	35	15	20	-	-	14,34 €	-	
MCL12-40/B	MCL12-40/SS/B	M12	40	15	20	-	-	15,80 €	93,08 €	
MCL12-50/B	MCL12-50/SS/B	M12	50	15	20	-	-	24,26 €	103,92 €	
MCL12-60/B	-	M12	60	15	20	-	-	30,80 €	-	

*Depending of availability - Dimensions in mm

Our other products




RPCtc
Swivel castor with central hole, Steel - Polyamide



PRF-SCREEN-5
Screen support, Support with 5 axes of rotation



SFWR
End support, Surface mounting



PB
Plastic deep groove ball bearing, Plastic - balls material : stainless steel



MDR
Dee shackle with eye bolt, Steel



V3RA_PT
3-spoked handwheel with handle, Polyamide



PRF-SCL
Lock for aluminium profile, Lock for sliding doors



PO
Pull handle - Multi-sector, Tapped recessed insert



GB-RA
Brass spur gear, Brass CuZn39Pb3



NPTR_M
Adjustable cross clamp, Adjustable



PSG05
Spur gear - precision range, Pre-hardened Steel 35NCD6



BLHB20
Right angled gearbox, bored shafts, up to 1.77 Nm

Complementary products



MCL
Cylindrical threaded sleeve, Cylindrical - stainless steel



TIF
Threaded rod - DIN975, Stainless steel A2



MHXred
Reducing sleeve male/female, Hexagonal - steel



MCLred
Reducing sleeve female/female, Cylindrical - steel