

- Module 1 to 3.5
- Moulded parts
- Material: Nylon 6 reinforced with 30% glass fibre
- Rough pilot bore after moulding


### Options

- We are unable to modify these parts

### Info.

- The 2 bevels should form a matching pair
- Moulded pre-bore must be machined to suit the application
- \*Pilot bore dimension given as a guide only

*ØA: pilot bore requires finishing*



**Economy range**

### DISCOUNTS

Qty	1+	10+	20+	50+	100+
Disc.	List	-10%	-15%	-25%	On request

Part number	Teeth		Pilot bore no guaranteed							L	Lm	Stock*	Price each 1 to 9
	Z	Module	ØDe	ØDp	B	F	ØDn	dm	ØA*				
MEB1-16	16	1,0	17,8	16,0	14,0	4	13	18,59	5	14,0	9,0	✓	4,94 €
MEB1.5-16	16	1,5	25,0	24,0	18,0	6	20	25,10	8	17,0	8,9	✓	6,22 €
MEB1.5-20	20	1,5	32,1	30,0	20,0	8	22	28,70	6	18,0	9,0	✓	6,92 €
MEB1.5-30	30	1,5	47,1	45,0	25,0	10	35	39,70	12	22,5	12,0	✓	10,27 €
MEB2-16	16	2,0	34,8	32,0	20,0	9	25	28,80	10	17,0	9,3	✓	8,65 €
MEB2-20	20	2,0	42,8	40,0	27,0	12	32	35,70	8	22,0	12,0	✓	12,20 €
MEB2-30	30	2,0	62,8	60,0	30,0	16	50	47,80	12	27,0	12,8	✓	16,62 €
MEB2.5-16	16	2,5	43,5	40,0	27,0	10	30	37,30	12	22,0	13,3	✓	10,83 €
MEB2.5-20	20	2,5	53,5	50,0	30,0	12	38	45,90	12	27,0	16,0	✓	12,57 €
MEB2.5-30	30	2,5	78,5	75,0	35,0	18	50	59,10	14	32,0	16,0	-	17,48 €
MEB3-16	16	3,0	52,2	48,0	30,0	12	38	44,20	11	26,0	16,2	✓	15,86 €
MEB3-20	20	3,0	64,2	60,0	35,0	18	44	51,10	14	31,0	13,6	✓	16,82 €
MEB3-30	30	3,0	94,2	90,0	40,0	22	60	68,10	20	36,0	19,0	✓	21,94 €
MEB3.5-20	20	3,5	74,9	70,0	40,5	22	56	58,60	14	36,0	19,0	-	On request

\* Depending on availability - Dimensions in mm

# Plastic bevel gear



## Ratio

# 2:1 - 3:1

- **Module 1.5 to 3**
- Moulded parts
- **Material:**  
Nylon 6 reinforced with 30% glass fibre

### Options

- We are unable to modify these parts


### Info.

- The 2 bevels should form a matching pair
- Moulded pre-bore must be machined to suit the application
- \*\*Pilot bore dimension given as a guide only




*ØA: Pilot bore requires finishing\*\**

## Moulded nylon PA6



**Ratio 2:1**



**Ratio 3:1**

**Economy range**

### DISCOUNTS

Qty	1+	10+	20+	50+	100+
Disc.	List	-10%	-15%	-25%	On request

Part number	Teeth		Pilot bore no guaranteed					ØA*	dm	L	Lm	Stock*	Price each 1 to 9
	Z	Module	ØDe	ØDp	B	F	ØDn						
<b>Ratio 2:1</b>													
MDB1.5-16	16	1,5	26,7	24	18,5	8	18	8	34,9	17,0	10,3	✓	7,80 €
MDB1.5-32	32	1,5	49,3	48	20,0	8	32	12	27,5	17,5	10,0	✓	13,38 €
MDB2-16	16	2,0	35,6	32	23,0	10	24	10	45,4	21,0	12,2	✓	9,10 €
MDB2-32	32	2,0	65,8	64	25,0	10	40	12	35,2	22,0	10,0	✓	19,96 €
MDB2.5-16	16	2,5	44,4	40	27,5	12	30	12	56,0	25,0	14,4	✓	11,75 €
MDB2.5-32	32	2,5	82,2	80	30,0	12	50	15	43,5	26,5	10,0	✓	24,75 €
MDB3-16	16	3,0	53,4	48	28,0	15	40	14	61,6	25,0	11,6	-	On request
MDB3-32	32	3,0	98,7	96	33,0	15	60	15	50,4	30,5	15,0	-	On request
<b>Ratio 3:1</b>													
MTB1.5-16	16	1,5	26,9	24	22,0	12	20	8	46,3	21,0	9,7	✓	On request
MTB1.5-48	48	1,5	72,9	72	21,0	12	42	15	29,2	19,0	12,0	✓	On request
MTB2.5-16	16	2,5	44,7	40	28,0	18	34	14	70,4	26,0	9,2	-	14,93 €
MTB2.5-48	48	2,5	121,6	120	32,0	18	60	20	44,6	27,0	16,0	-	28,69 €
MTB3-16	16	3,0	53,7	48	30,0	18	35	10	84,2	28,0	11,2	-	On request
MTB3-48	48	3,0	145,9	144	38,0	18	50	20	54,1	32,0	19,0	-	On request

\*Depending on availability - Dimensions in mm

**Moulded** nylon 6

Ratio

**1.5:1 - 4:1**


- Module 2 to 3
- Moulded parts
- Material:  
Nylon 6 reinforced with 30% glass fibre

## Options


- We are unable to modify these parts

## Info.


- The 2 bevels should form a matching pair
- Moulded pre-bore must be machined to suit the application
- \*Pilot bore dimension given as a guide only



*ØA: pilot bore requires finishing*



Ratio 4:1



Ratio 1.5:1

**Economy range**

## DISCOUNTS

Qty	1+	10+	20+	50+	100+
Disc.	List	-10%	-15%	-25%	On request

Part number	Teeth		Module	ØDe	ØDp	B	F	ØDn	ØA*	dm	L	Lm	Stock*	Price each 1 to 9
	Z	Module												
<b>Ratio 4:1</b>														
MFB2.5-16	16	2,5	44,9	40	30,5	18	32	15	92,6	29,0	11,7	✓	14,02 €	
MFB2.5-64	64	2,5	161,2	160	35,0	18	80	20	48,8	30,0	16,0	✓	60,42 €	
MFB3-16	16	3,0	53,8	48	32,0	20	35	10	108,0	30,0	11,1	✓	26,19 €	
MFB3-64	64	3,0	193,5	192	42,0	20	60	19	58,8	36,0	22,0	✓	52,72 €	
<b>Ratio 1,5:1</b>														
MHB2-20	20	2,0	43,3	40	23,0	10	30	8	43,3	23,0	10,2	-	On request	
MHB2-30	30	2,0	62,2	60	27,0	10	50	11	40,6	27,5	15,2	-	On request	

\* Depending on availability - Dimensions in mm