

Shackle with eye bolt



MDR


Pin diameters 5-20mm

- **Lifting shackle**
- Marked with pin diameter, SWL and CE mark
- Material:
Shackle: Steel Fe430B zinc treated



Info.

- SWL: SAFE WORKING LOAD.
The Safe Working Load is calculated by dividing the Breaking Strength by a factor of safety of 5.
- **Not sold individually, please contact us for details.**



DISCOUNTS

Qty	1+	5+	10+	20+	30+	50+
Disc.	List	-5%	-10%	-15%	-20%	On request


Part number	Pin ØD	A	B	ØC	ØE	F	SWL (kg)	Weight (kg)	Stock*	Price each 1 to 4
MDR1-05	5	8	18	13	6	23	100	0,020	✓	1,79 €
MDR1-06	6	12	25	14	6	29	160	0,040	✓	2,14 €
MDR1-08	8	15	32	18	8	37	250	0,070	✓	3,07 €
MDR1-10	10	18	38	22	10	41	400	0,140	✓	3,87 €
MDR1-12	12	26	50	27	12	56	630	0,260	✓	6,11 €
MDR1-14	14	27	56	29	14	57	800	0,370	✓	7,49 €
MDR1-16	16	31	64	35	17	64	1000	0,560	✓	10,05 €
MDR1-18	18	32	70	36	19	65	1300	0,710	-	13,90 €
MDR1-20	20	38	78	40	20	69	1600	0,940	✓	17,52 €

*Depending on availability - Dimensions in mm

- Lifting shackle
- Material: Stainless steel 316

Info.

- SWL: SAFE WORKING LOAD.
The Safe Working Load is calculated by dividing the Breaking Strength by a factor of safety of 5.

**DISCOUNTS**

Qty	1+	5+	10+	20+	30+
Disc.	List	-5%	-10%	-15%	On request

Part number	Pin ØD	A	L	H	SWL (kg)	Weight (kg)	Stock*	Price each 1 to 4
MDR1-05/SS	5	9,5	23,0	33	190	0,015	✓	3,49 €
MDR1-06/SS	6	12,0	24,0	37	360	0,030	✓	3,66 €
MDR1-08/SS	8	16,0	35,0	50	540	0,060	✓	4,36 €
MDR1-10/SS	10	19,3	45,6	65	720	0,125	✓	6,27 €
MDR1-12/SS	12	27,0	48,0	72	1080	0,200	✓	11,21 €
MDR1-14/SS	14	28,0	57,0	83	1260	0,310	-	16,64 €
MDR1-16/SS	16	32,8	59,0	89	1680	0,510	✓	26,69 €
MDR1-20/SS	19	38,0	88,0	124	2400	0,900	-	52,49 €

*Depending on availability - Dimensions in mm