



Bevel gear for use in food industry


Moulded blue PA6 Nylon

Ratio
1:1

- Moulded gear for use in food applications
- Pressure angle: 20°
- Material:
Blue glass-fibre reinforced Polyamide
- Two identical gears must be ordered to make a pair

Info

- *Pre-bore after de-moulding, must be machined before installation.
- We are unable to modify these products



DISCOUNTS

Qty	1+	10+	20+	50+	100+
Disc.	Net	-10%	-15%	-25%	On request

Part N°	Teeth Z	Module	ØDe	ØDp	B	F	ØM Hub	ØA* Pre-bore	dm	L	Lm	Price each. 1 to 9
MEB1-16/ALI	16	1	17,4	16	14	4,0	13,5	5	18,59	14,0	9,5	6,65 €
MEB1.5-16/ALI	16	1,5	26,1	24	18	5,5	20,0	8	25,1	18,0	12	8,40 €
MEB1.5-20/ALI	20	1,5	32,1	30	20	10,0	22,5	6	28,7	20,0	8,5	9,35 €
MEB1.5-30/ALI	30	1,5	47,1	45	25	10,0	34,5	12	39,7	25,0	13	13,85 €
MEB2-16/ALI	16	2	34,8	32	20	9,0	25,0	9	28,8	20,0	9	11,68 €
MEB2-20/ALI	20	2	42,8	40	27	13,0	32,5	9	35,7	27,0	13,5	16,40 €
MEB2-30/ALI	30	2	62,8	60	30	16,0	50,5	12	47,8	30,0	12,8	22,35 €
MEB2.5-16/ALI	16	2,5	43,5	40	28	10,0	30,0	12	37,3	28,0	15,5	16,95 €
MEB2.5-20/ALI	20	2,5	53,5	50	30	12,5	38,5	12	45,9	26,0	16	23,51 €
MEB2.5-30/ALI	30	2,5	78,5	75	35	18,0	51,0	14	59,1	31,0	15,5	21,33 €
MEB3-16/ALI	16	3	52,2	48	31	13,0	38,0	11	44,2	31,0	16,2	15,85 €
MEB3-20/ALI	20	3	64,2	60	35	18,0	43,5	14	51,1	35,0	15	22,59 €
MEB3-30/ALI	30	3	94,2	90	40	22,0	61,0	20	68,1	36,5	18,5	29,49 €
MEB3.5-20/ALI	20	3,5	74,9	70	39	22,0	56,5	14	58,6	35,5	16,5	25,32 €

All dimensions in mm

0 825 88 6000
Service 0,15 € / min
+ prix appel

cial2@hpceurope.com

HPC SUPPLEMENT 2019

Our other products



T2,5-BAR
T type tooth bar
stock, T2.5



DKONSL
Silicone conical elasto
buffer, Male mounting



CHTRP
Single and dual
output gearboxes, Up
to 28,8 Nm



T39_T49
Extension spring in
metre length steel, by
the metre



KSTM
Igubal® pillow block
bearing, Polymer



H4
Crossed helical gear
crossed axis at 90°,
Steel 20NCD2



UGH32
H Type Guide units,
For Ø32 actuators



ETP
Modular handle for
aluminium profile,
Modular handle



DOMI_MD
Domino rotary table,
40/1



HBM
Adjustment bushing
for half-rail guide,
Adjustment bushing



TAD
Threaded adjustable
feet, Plastic and steel



ACLALF
Adjustable foot for
aluminium profile,
Ideal for workstations

Complementary products