

Hexagonal threaded sleeves

Stock **Sta** **Ste**

MHX

Steel or **stainless steel**

- Hexagonal sleeves, through threaded
- Suitable for joining threaded bars
- Materials:
Zn3-5BL galvanised steel S300Pb
Stainless steel 303


Info.

- Sold by the packet

Accessory

- Threaded bar TIFss (tome 1 p.529)

steel or stainless steel



DISCOUNTS

Qty	1+	5+	20+	50+
Disc.	List	-5%	-10%	On request

Part number		Thread	ØT	L	AF	Qty per packet	Stock*		Price per packet 1 to 4	
Steel	Stainless steel						Steel	Stainless steel	Steel	Stainless steel
MHX3-10/B	MHX3-10/SS/B	M3	10	5,5	20	✓	-	4,17 €	15,67 €	
MHX3-12/B	MHX3-12/SS/B	M3	12	5,5	20	-	-	4,29 €	17,43 €	
MHX3-15/B	MHX3-15/SS/B	M3	15	5,5	20	✓	-	4,82 €	19,26 €	
MHX3-18/B	-	M3	18	5,5	20	-	-	5,36 €	-	
MHX3-20/B	-	M3	20	5,5	20	✓	-	5,82 €	-	

*Depending on availability - Dimensions in mm

DISCOUNTS

Qty	1+	5+	20+	50+
Disc.	List	-5%	-10%	On request

Part number		Thread			Qty per packet	Stock*		Price per packet 1 to 4	
Steel	Stainless steel	ØT	L	AF		Steel	Stainless steel	Steel	Stainless steel
MHX4-10/B	MHX4-10/SS/B	M4	10	7,0	20	-	✓	4,37 €	18,20 €
MHX4-12/B	MHX4-12/SS/B	M4	12	7,0	20	-	-	4,68 €	20,46 €
MHX4-15/B	MHX4-15/SS/B	M4	15	7,0	20	-	-	5,18 €	22,87 €
MHX4-18/B	-	M4	18	7,0	20	-	-	5,70 €	-
MHX4-20/B	-	M4	20	7,0	20	✓	-	6,48 €	-
-	MHX5-12/SS/B	M5	12	8,0	20	-	✓	-	32,06 €
MHX5-15/B	MHX5-15/SS/B	M5	15	8,0	20	-	-	6,68 €	24,29 €
-	MHX5-18/SS/B	M5	18	8,0	20	-	-	-	26,91 €
MHX5-20/B	MHX5-20/SS/B	M5	20	8,0	20	✓	✓	9,78 €	27,38 €
MHX5-25/B	-	M5	25	8,0	20	-	-	9,33 €	-
MHX6-15/B	MHX6-15/SS/B	M6	15	10,0	20	✓	✓	5,46 €	35,03 €
MHX6-18/B	MHX6-18/SS/B	M6	18	10,0	20	-	-	5,53 €	34,19 €
MHX6-20/B	MHX6-20/SS/B	M6	20	10,0	20	-	-	6,01 €	35,71 €
MHX6-25/B	MHX6-25/SS/B	M6	25	10,0	20	✓	✓	6,13 €	40,81 €
MHX6-30/B	MHX6-30/SS/B	M6	30	10,0	20	✓	✓	9,41 €	48,45 €
MHX6-35/B	-	M6	35	10,0	20	✓	✓	11,21 €	-
MHX6-40/B	-	M6	40	10,0	20	✓	✓	11,85 €	-
MHX6-50/B	-	M6	50	10,0	20	-	-	18,03 €	-
MHX8-15/B	-	M8	15	13,0	20	✓	-	8,97 €	-
MHX8-20/B	-	M8	20	13,0	20	✓	-	10,41 €	-
MHX8-25/B	MHX8-25/SS/B	M8	25	13,0	20	✓	-	13,26 €	63,30 €
MHX8-30/B	MHX8-30/SS/B	M8	30	13,0	20	✓	✓	13,57 €	73,51 €
MHX8-35/B	-	M8	35	13,0	20	-	-	21,51 €	-
MHX8-40/B	-	M8	40	13,0	20	✓	-	17,01 €	-
MHX8-45/B	-	M8	45	13,0	20	✓	-	29,03 €	-
MHX8-50/B	-	M8	50	13,0	20	✓	-	27,86 €	-
MHX8-60/B	-	M8	60	13,0	20	✓	-	41,13 €	-
MHX10-20/B	-	M10	20	17,0	20	✓	-	14,86 €	-
MHX10-25/B	MHX10-25/SS/B	M10	25	17,0	20	-	-	16,98 €	108,28 €
MHX10-30/B	MHX10-30/SS/B	M10	30	17,0	20	-	-	18,95 €	117,45 €
MHX10-40/B	MHX10-40/SS/B	M10	40	17,0	20	✓	-	25,60 €	171,59 €
MHX10-50/B	-	M10	50	17,0	20	-	-	35,93 €	-
MHX10-60/B	-	M10	60	17,0	20	-	-	108,83 €	-
MHX10-70/B	-	M10	70	17,0	20	✓	-	113,52 €	-
MHX12-25/B	-	M12	25	19,0	20	✓	-	18,07 €	-
MHX12-30/B	MHX12-30/SS/B	M12	30	19,0	20	-	-	23,63 €	132,79 €
MHX12-40/B	MHX12-40/SS/B	M12	40	19,0	20	✓	-	34,82 €	180,77 €
MHX12-50/B	MHX12-50/SS/B	M12	50	19,0	20	✓	-	42,63 €	260,47 €
MHX12-60/B	-	M12	60	19,0	20	-	-	115,31 €	-
MHX12-70/B	-	M12	70	19,0	20	✓	-	122,94 €	-

*Depending on availability - Dimensions in mm