


- Male/female pillar
- Material:
stainless steel 303
- Sold by the packet



DISCOUNTS

N° packets	1+	5+	20+	100+
Discount	Prix -20%	-30%	On request	

Part number	Thread	ØM	L1	L2	L3	AF	Qty. per packet	Stock*	Price per packet
MPS3-5/B	M3		5	3	8	5,50	20	✓	22,42 €
MPS3-8/B	M3		8	4	8	5,50	20	✓	22,99 €
MPS3-10/B	M3		10	6	8	5,50	20	✓	23,38 €
MPS3-12/B	M3		12	8	8	5,50	20	✓	24,94 €
MPS3-15/B	M3		15	8	8	5,50	20	✓	25,52 €
MPS3-18/B	M3		18	8	8	5,50	20	✓	26,14 €
MPS3-20/B	M3		20	8	8	5,50	20	✓	26,48 €
MPS3-25/B	M3		25	10	10	5,50	20	✓	29,76 €
MPS4-5/B	M4		5	3	8	7,00	20	✓	23,33 €
MPS4-10/B	M4		10	6	8	7,00	20	✓	24,76 €
MPS4-15/B	M4		15	8	8	7,00	20	✓	27,36 €
MPS4-20/B	M4		20	8	8	7,00	20	✓	28,79 €
MPS4-25/B	M4		25	10	10	7,00	20	✓	32,68 €

*Depending on availability - Dimensions in mm

Our other products



J53
Spur gear coaxial gearbox, from 0.43 to 1.15 - In-line



HCV
V-rail guidance Simple Select® system, on rail



HTD14M_55
HTD Heavy duty timing pulley, HTD14 Steel



BLH20
Right angled gearbox, from 0.53 to 1.77



PGMSS
Stainless steel pull handle, Stainless steel



GE
Toggle latches, Miniature



DCG
Suction cup, 2.5 bellows, nitrile




IN0
Internal gear, Steel 20NCD2




BOXdh
Boxed set of cylindrical dowel pins DIN6325, Boxed set -



DOMI120
Domino 120 adjustable slide, Slide DOMILINE 120



TBV
Manual lifting tables, 12kg



M0
Worm and wheel set, Machined plastic (delrin)

Complementary products



HS
Hexagonal spacer, Stainless steel 303