


- Male/female pillar
- Material:  
stainless steel 303
- Sold by the packet



### DISCOUNTS

N° packets	1+	5+	20+	100+
Discount	Prix -20%	-30%	On request	

Part number	Thread	ØM	L1	L2	L3	AF	Qty. per packet	Stock*	Price per packet
MPS3-5/B	M3		5	3	8	5,50	20	✓	22,42 €
MPS3-8/B	M3		8	4	8	5,50	20	✓	22,99 €
MPS3-10/B	M3		10	6	8	5,50	20	✓	23,38 €
MPS3-12/B	M3		12	8	8	5,50	20	✓	24,94 €
MPS3-15/B	M3		15	8	8	5,50	20	✓	25,52 €
MPS3-18/B	M3		18	8	8	5,50	20	✓	26,14 €
MPS3-20/B	M3		20	8	8	5,50	20	✓	26,48 €
MPS3-25/B	M3		25	10	10	5,50	20	✓	29,76 €
MPS4-5/B	M4		5	3	8	7,00	20	✓	23,33 €
MPS4-10/B	M4		10	6	8	7,00	20	✓	24,76 €
MPS4-15/B	M4		15	8	8	7,00	20	✓	27,36 €
MPS4-20/B	M4		20	8	8	7,00	20	✓	28,79 €
MPS4-25/B	M4		25	10	10	7,00	20	✓	32,68 €

\*Depending on availability - Dimensions in mm

## Our other products



Drylin® W rail, Rail



Fixed tube carrier,  
Fixed  $\varnothing$ 10 to  $\varnothing$ 14



Stainless steel  
spherical bearing,  
Stainless steel / PTFE



Hexagonal headed  
bolts, Steel class 8.8



Box set of washer -  
DIN125, Box set of  
steel washers



Idler sprocket for slat  
top chain, Ranges 821  
and 805



Stem support for  
caster, For swivel  
caster with central  
hole



High helix leadscrew,  
Cylindrical nut - up to  
40mm per rotation



Spacer for tube  
carrier, Fixing  
accessory  $\varnothing$ 10 to  $\varnothing$ 14



Toggle latches,  
Miniature



Moulded plastic bevel  
gear (nylon), 2:1



Panamech, Multi-  
Beam stainless steel,  
Stainless steel - with  
clampin...

## Complementary products



Hexagonal spacer,  
Stainless steel 303