Stainless steel Quick link

Link diameter 4-12mm

MRASS


- For joining or closing chains

- Screw to secure
- Fully tighten to ensure safety
- Material: Stainless steel 316 Rina/nut X2CrNi

Info.

- SWL: safe working load. The Safe Working Load is calculated by dividing the Breaking Strength by a factor of safety of 3.





DISCOUNTS

Qty	1+	5+	10+	20+	30+ On request
)isc.	List	-5%	-10%	-15%	On request

							SWL	Weight for 100	Charlet	Price each
Part number	ØD	L2	L1	L	P	E	(kg)	pieces (kg)	Stock*	1 to 4
MRA1-04/SS	4	40,0	32,0	11,0	6,0	12,0	280	1,200	~	8,64 €
MRA1-05/SS	5	48,0	38,0	12,0	7,0	16,0	450	2,100	V	9,65 €
MRA1-06/SS	6	57,0	45,0	14,0	9,0	19,0	650	3,540	V	12,32 €
MRA1-07/SS	7	66,0	52,0	16,0	8,0	21,0	900	5,230	-	16,76 €
MRA1-08/SS	8	73,0	57,0	17,0	12,0	24,0	1100	7,900	-	16,76 €
MRA1-09/SS	9	80,0	62,0	19,0	11,0	26,0	1400	10,500	-	25,33 €
MRA1-10/SS	10	89,0	69,0	20,0	13,0	29,0	1800	14,050	-	30,66 €
MRA1-12/SS	12	105,0	81,0	23,0	16,0	34,0	2500	23,200	V	48,83 €

^{*}Depending on availability - Dimensions in mm





Our other products



High rigidity linear slide, Rail - from 9320 N to 71300 N



Hexagonal shaft, Hexagonal shaft



Single row cylindrical roller bearing, Free inner ring



Spherical tilt washer -DIN6319, concave



H Type Guide units, For Ø25 actuators



Sleeve for splined ball shaft, Chariot - from 514 N to 15386 N



AT type timing belt per metre, AT5 Steel cored polyurethane



Worm and wheel set, Machined plastic (delrin)



Coupling bar for aluminium profile,



2A motorised linear actuator, 2 amperes



Adjustable latch clamp with strike



Worm - precision range, Steel

Complementary products



Straight long link stainless steel chain, Stainless steel



Low cost stainless steel quick link, Stainless steel



Low cost quick link, Steel



Quick link, Steel