

- For joining or closing chains
- White chromed steel
- **Low cost range, no SWL specified**
- Engraved with ring diameter




**Economy range**

### Application

- Nominal load figures are given as an indication only
- Should not be used for lifting (load values not guaranteed)

### Info

- Also available in stainless steel



### DISCOUNTS

Qty	1+	20+	40+	60+	80+	100+
Disc.	List	-5%	-10%	-15%	-20%	On request

Part number	ØD	A	B	C	E	Nominal load (kg)	Weight (g)	Stock*	Price each 1 to 19
MRA1-03/ECO	3,5	36,0	10,0	5,0	12,0	100	8	✓	0,48 €
MRA1-04/ECO	4,0	39,5	11,5	6,0	14,0	180	12	✓	0,61 €
MRA1-05/ECO	5,0	49,5	13,0	7,0	17,0	280	22	-	0,66 €
MRA1-06/ECO	6,0	57,0	14,5	8,0	20,0	400	36	✓	0,81 €
MRA1-07/ECO	7,0	66,0	16,0	9,0	22,5	550	52	-	1,15 €
MRA1-08/ECO	8,0	74,0	17,5	10,0	24,0	700	76	✓	1,31 €
MRA1-09/ECO	9,0	80,0	19,0	11,0	27,0	900	110	-	1,89 €
MRA1-10/ECO	10,0	89,0	20,5	12,0	30,0	1100	146	-	2,48 €
MRA1-12/ECO	12,0	104,5	23,5	14,0	34,0	1500	234	-	3,97 €
MRA1-14/ECO	14,0	121,0	26,5	17,0	39,0	2200	358	-	8,96 €
MRA1-16/ECO	16,0	140,0	29,5	19,0	43,0	2900	520	-	12,47 €

\*Depending on availability - Dimensions in mm

- For joining or closing chains
- Stainless steel 316
- Low cost range, no SWL specified

### Application

- Nominal load figures are given as an indication only
- Should not be used for lifting (load values not guaranteed)


### Info

- Also available in steel



stainless steel

Economy range



### DISCOUNTS

Qty	1+	20+	40+	60+	80+	100+
Disc.	List	-5%	-10%	-15%	-20%	On request

Part number	ØD	A	L1	L	C	E	Nominal load (kg)	Weight (g)	Stock*	Price each
										1 to 19
MRA1-03/SS/ECO	3,5	37,2	30,4	9,7	5,5	12,6	220	8	✓	3,20 €
MRA1-04/SS/ECO	4,0	41,0	33,0	11,7	6,3	12,7	280	12	✓	3,48 €
MRA1-05/SS/ECO	5,0	51,2	41,0	13,0	7,0	17,0	450	22	✓	3,94 €
MRA1-06/SS/ECO	6,0	59,0	47,0	14,7	8,8	20,0	650	36	✓	4,45 €
MRA1-07/SS/ECO	7,0	67,7	54,0	18,3	9,7	23,7	900	54	-	7,64 €
MRA1-08/SS/ECO	8,0	74,6	59,0	18,3	9,9	25,0	1100	76	✓	8,94 €
MRA1-10/SS/ECO	10,0	89,0	70,0	22,2	12,8	30,0	1800	138	-	15,46 €
MRA1-12/SS/ECO	12,0	105,0	82,0	24,8	14,2	34,0	3500	224	-	24,75 €

\* Depending on availability - Dimensions in mm