Double cross clamp

New Alu

NDS

Crossed or parallel


- ***For Ø20 tubes or shafts***
- *Multiple connection possibilities, either at right angles or for extending length of tubular elements*
- *Material :*
  Aluminium with steel screws

Advantages


- *Clip on, tool free assembly*




Crossed version



Parrallel version



NDS-20/C



NDS-20/P

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	Type	ØA	B	C	D	H	E	Weight (g)	Price each 1 to 9
NDS-20/C	crossed	20	22	24	60	-	-	58	26,87 €
NDS-20/P	parallel	20	26	64	14	25	12,5	60	24,92 €

Dimensions in mm

Our other products



PSG08S

Spur gear - precision range, Stainless steel 303



ASH

Hoist ring for welding, for straight lifts - for welding




CHAE4060PA

Decorative asymmetric screwed hinge, Polyamide



DOG111

Motor-gearbox 12V and 24V DC, from 1.5 to 6 Nm



PRZ

Wear strip for slat top chain, Z profile to be clipped



BFM2

Flanged bronze nut, Bronze - 2 threads



EP7

Electronic digital position indicator, 5 numbers



LSM

Stainless steel 316L leadscrew, Stainless steel - 1 thread



KB_OP

Open precision linear bearing, Precision - steel



GE

Toggle latches, Miniature



BLHB60

Right angled gearbox, bored shafts, up to 70 Nm



DOMI50

Domino 50 adjustable slide, Slide DOMILINE 50

Complementary products



NDS20

Double cross clamp, Parallel