
Multiple junction clamp

NJM


For rod or tube

- ***For extending cylindrical sections, either in-line or parallel mounting***
- *Materials:*
  Wing knob: thermosetting plastic
  Colour: dark grey
  Screw: resistance class 5.8, yellow chromate plated steel
  Body: high-resistance anodised aluminium




Advantages

- *Parallel mounting arrangement can be used to strengthen a structure*
- *Additional holes in body allow orthogonal joints to be assembled*



Positions:



DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-10%	On request

Part number	ØD	ØD1	ØD2	L	L1	L2	L3	L4	H	H1	H2	Weight (kg)	Stock*	Price each 1 to 4
NJM-8	8	28	M8	89	36	17	20	8	50	24	15	0,074	-	44,11 €
NJM-10	10	32	M8	90	40	19	20	10	50	24	15	0,093	✔	46,17 €
NJM-12	12	36	M8	90	44	21	20	12	50	24	15	0,118	-	52,79 €
NJM-16	16	45	M10	126	56	27	24	16	75	35	20	0,262	-	67,34 €

**Depending on availability - Dimensions in mm*

Our other products



PRFbou

Emergency release button for aluminium profile, Emergency release bu...



CHA38_SS

Stainless steel face frame hinge, Surface mount



ZDB

Machined plastic bevel gear , 2:1



TPR

High helix leadscrew, Leadscrew only - up to 40mm per rotation



RFV40

Stainless steel worm and wheel gearbox, up to 47 Nm



SVR20

Screwjack with travelling nut, with moving nut



NANO

Speed controller 3A, 3 A



GLB

Small 6 lobe threaded handle - female, Technopolymer - Brass



BUH77

Motor-gearbox 12V and 24V DC, from 0.1



BOXKK

Boxed set of DIN6885A keys,



STL

Guidance brush - Rail, Rail



CHA_GC_14SS

Stainless steel garnet hinge, To screw

Complementary products



NSA

Adjustable clamp, Articulated



NSR

Adjustable clamp, Adjustable