Orthogonal support clamp

NRV

Easy to mount and adjust

- **90° support clamp**
- Material:
  stainless steel




Application

- Supporting sensors, connecting tubes when assembling small structures

Accessories

- To be used with **MBF** sleeves and **APBC** rods

Suitable for food industry use



DISCOUNTS

Qty	1+	5+	10+	20+
Disc.	List	-5%	-10%	On request

Part number	For rod ØA1	Thread ØM1	For rod ØA2	Thread ØM2	Used with sleeve	Stock*	Price each 1 to 4
NRV8-8	8	M12x1,5	8	M12x1,5	MBF8-12	✔	10,45 €
NRV8-10	8	M12x1,5	10	M14x1,5	MBF8-12/MBF10-14	✔	10,56 €
NRV8-12	8	M12x1,5	12	M16x1,5	MBF8-12/MBF12-16	✔	10,99 €
NRV10-10	10	M14x1,5	10	M14x1,5	MBF10-14	✔	10,63 €
NRV10-12	10	M14x1,5	12	M16x1,5	MBF10-14/MBF12-16	-	10,75 €
NRV12-12	12	M16x1,5	12	M16x1,5	MBF12-16	✔	11,06 €

*Depending on availability - Dimensions in mm

Our other products


MEB

Moulded plastic bevel gear (nylon), 1:1


MAX22

Motor-gearbox 12V and 24V DC, from 0,07 to 0,2Nm


T5-10ECO


T type timing pulley, Economy range - T5 aluminium


BOXsap

Boxed set of spring pins ISO8752, Boxed set - Split ISO 8752


HK

Manual locking clamp, Manual locking clamp T


E40

Right angle helical reducers, from 2.30 to 20 Nm


BDP2R

Adjustable support arm, Increased grip


PRF-SRA

Lock for aluminium profile, Lock


SSDB

Stainless steel bevel gear, 2:1


DFG

Flat suction cup, silicon



ACLEPP

Right angled bracket for aluminium profile,


PLM-20SC

Cylindrical magnet, Cylindrical magnet

Complementary products


APBC

Circular rod, Round rod


MBF

Threaded blocking clamp, Threaded locking clamp