# Right angled support clamp

## NSP

### Easy to mount and adjust

- ***Support clamp for use with 8 mm T slots***
- *Material:*
  *stainless steel*





## Application


- *Supporting sensors, connecting tubes when assembling small structures*

## Accessories

- *To be used with* ***MBF*** *sleeves and* ***APBC*** *rods*

**Suitable for food industry use**




## DISCOUNTS

| Qty | 1+ | 5+ | 10+ | 20+ |
|---|---|---|---|---|
| Disc. | List | -5% | -10% | On request |

| Part number | For rod ØA | Thread ØM | H | B | L | Used with sleeve | Stock* | Price each 1 to 4 |
|---|---|---|---|---|---|---|---|---|
| NSP8-12 | 8 | M12x1,5 | 0-10 | 8 | 13 | MBF8-12 | ✔ | 16,98 € |
| NSP10-14 | 10 | M14x1,5 | 0-10 | 8 | 13 | MBF10-14 | ✔ | 17,20 € |
| NSP12-16 | 12 | M16x1,5 | 0-10 | 8 | 13 | MBF12-16 | ✔ | 17,49 € |

**Depending on availability - Dimensions in mm*

# Our other products


CHB

Worm and wheel gear reducer, up to 22 Nm


PRF_PSA

Shaft support for aluminium profile, Linear guide shaft


CHAR5050_Z

Spring hinge, screwed


BOX-TOR-TOOL

Box set of tool for Nitrile O-rings, Extraction tools


ACM_AZ

Mounting bracket for bonnet fastener, Hook


CHTRP

Single and dual output gearboxes, Up to 87,3 Nm


MFBSC

Stainless steel flexible bellows coupling, Stainless steel - with cl...


BPHF

Ball transfer unit push fit, Heavy


RT70

Self-centering locking Assembly,


RESC

Retractable castor for aluminium profile,


SH3

Parallel axis helical gear, Steel 20NCD2



TS01_TW01

Drylin® T linear slide, up to 7000 N

## Complementary products


MBF

Threaded blocking clamp, Threaded locking clamp


APBC

Circular rod, Round rod