Universal 90° support clamp

NSU

Easy to mount and adjust

- ***Support clamp with adjustable head***
- *Head can be adjusted by loosening and then tightening countersunk screw before assembly*
- *Material:*
  stainless steel




Application


- *Supporting sensors, connecting tubes when assembling small structures*

Accessories

- *To be used with* ***MBF*** *sleeves and* ***APBC*** *rods*

Suitable for food industry use





DISCOUNTS

Qty	1+	5+	10+	20+
Disc.	List	-5%	-10%	On request

Part number	For rod ØA	Thread ØM	Used with sleeve	Stock*	Price each 1 to 4
NSU8-12	8	M12x1,5	MBF8-12	✔	13,27 €
NSU10-14	10	M14x1,5	MBF10-14	✔	13,46 €
NSU12-16	12	M16x1,5	MBF12-16	✔	13,65 €

**Depending on availability - Dimensions in mm*

Our other products



LVTMFC

Device for controlling limit switches, For mini-actuator LVT



ZBconique

Machined plastic bevel gear, 1:1



DOMI120

Accessories, Fixing kit



GMK17_BR

Clamp for guiding profile, Rounded only - single



DOMI30

Domino 30 adjustable slide, Slide DOMILINE 30



MEB

Moulded plastic bevel gear (nylon), 1:1



DB

Steel bevel gear, 2:1



MHX

Hexagonal threaded sleeve, Hexagonal - stainless steel



ATZY

Diabolo shaped elasto mount, Steel



TOC

Short swivel head, Short



SCA_SS

Stainless steel flat cable clamp, Stainless steel



MDR_SS


Stainless steel Dee shackle with eye bolt, Stainless steel

Complementary products



MBF

Threaded blocking clamp, Threaded locking clamp



APBC

Circular rod, Round rod