Articulated pressed steel feet Ø80

Maximum load 20,000N

PARF80

Economical




- **Swivelling mounting foot with steel mounting plate**
- Materials:
  Base - chromed steel plate
  Threaded shaft - chromed steel

Usage

- The threaded shaft is free to rotate
- A nut under the mounting base allows both rotation and angular inclination (+/-4°) movement to be restricted and means these feet can be used to support posts with recessed holes or mounting plates used with a nut and locknut.
- Angular blocking reduces noise and any lever effect on the mountings (avoids risk of being pulled out)

Advantage

- Ideal for floor mounting robots and also increased speed of production



DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØM	B	S	A	SW	G	H	Static load (N)	Price each 1 to 5
PARF80-16-150	M16	150	3	39,5	13	19	189,5	20000	19,11 €
PARF80-16-200	M16	200	3	39,5	13	19	239,5	20000	20,40 €
PARF80-20-150	M20	150	3	40,5	17	19	190,5	20000	21,88 €
PARF80-20-200	M20	200	3	40,5	17	19	240,5	20000	23,77 €

Dimensions in mm

Articulated pressed steel feet Ø10 Ste

PARF110 Maximum load 30,000N

- ***Swivelling mounting foot with steel mounting plate***
- *Materials:*
  Base - chromed steel plate
  Threaded shaft - chromed steel

Economical




Usage

- *The threaded shaft is free to rotate*
- *A nut under the mounting base allows both rotation and angular inclination (+/-4°) movement to be restricted and means these feet can be used to support posts with recessed holes or mounting plates used with a nut and locknut.*
- *Angular blocking reduces noise and any lever effect on the mountings (avoids risk of being pulled out)*

Advantage

- *Ideal for floor mounting robots and also increased speed of production*



DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØM	B	S	A	SW	G	H	Static load (N)	Price each 1 to 5
PARF110-16-150	M16	150	4	41	17	19	191	25000	22,00 €
PARF110-16-200	M16	200	4	41	17	19	241	25000	23,21 €
PARF110-20-150	M20	150	4	42	17	19	192	25000	24,66 €
PARF110-20-200	M20	200	4	42	17	19	242	25000	26,70 €
PARF110-24-150	M24	150	4	43	20	19	193	30000	29,25 €
PARF110-24-200	M24	200	4	43	20	19	243	30000	32,24 €

Dimensions in mm