Pressed stainless steel articulated foot

Maximum load 12,000N — PAT85ss

- **Articulated foot**
- **Tilt: +/- 4° from vertical**
- Materials:
  Base and spindle: stainless steel 1.4301 (304)
  Sole: vulcanised rubber (Shore hardness 80)
  Base: Ø85mm




Uses

- Laboratory furniture
- Medical and food industries

Note

- Values for static load given at 50% of rod length. With dynamic or vibrating loads, value will be lower.



DISCOUNTS

Qty	1+	6+	10+	15+
Disc.	List	-5%	-10%	On request

Part number	S	B	ØD	A/F	M	G	H (N)	Static load (N)	Stock*	Price each 1 to 5
PAT85-16-100/SS	7	100	85	13	M16	16	130	12000	✔	56,17 €
PAT85-16-150/SS	7	150	85	13	M16	16	180	12000	-	59,10 €
PAT85-16-175/SS	7	175	85	13	M16	16	205	12000	✔	61,97 €
PAT85-20-100/SS	7	100	85	17	M20	16	130	12000	-	59,10 €
PAT85-20-150/SS	7	150	85	17	M20	16	180	12000	✔	61,80 €
PAT85-20-200/SS	7	200	85	17	M20	16	230	12000	-	63,71 €

**Depending on availability - Dimensions in mm*

Pressed stainless steel articulated foot Sta Eco

PAT123ss — Maximum load 20,000N

- **Articulated foot**
- **Swivel: +/- 4° from vertical**
- Materials:
  Base and spindle: stainless steel 1.4301 (304)
  Sole: vulcanised rubber (Shore hardness 80)
- Base Ø123mm




Uses

- Laboratory furniture
- Medical and food industries

Note

- Values for static load given at 50% of rod length. With dynamic or vibrating loads, value will be lower



DISCOUNTS

Qty	1+	6+	10+	15+
Disc.	List	-5%	-10%	On request

Part number	S	B	ØD	A/F	M	G	H (N)	Static load (N)	Stock*	Price each 1 to 5
PAT123-16-100/SS	7	100	123	13	M16	23,5	137	20000	✔	74,96 €
PAT123-16-150/SS	7	150	123	13	M16	23,5	187	20000	-	77,91 €
PAT123-16-175/SS	7	175	123	13	M16	23,5	212	20000	✔	81,83 €
PAT123-20-100/SS	7	100	123	17	M20	23,5	137	20000	-	78,07 €
PAT123-20-150/SS	7	150	123	17	M20	23,5	187	20000	-	78,68 €
PAT123-20-200/SS	7	200	123	17	M20	23,5	237	20000	✔	81,02 €
PAT123-24-100/SS	7	100	123	20	M24	23,5	138	20000	-	79,43 €
PAT123-24-150/SS	7	150	123	20	M24	23,5	188	20000	-	81,02 €
PAT123-24-200/SS	7	200	123	20	M24	23,5	238	20000	-	83,93 €
PAT123-30-150/SS	7	150	123	26	M30	23,5	188	20000	-	91,28 €
PAT123-30-200/SS	7	200	123	26	M30	23,5	238	20000	-	100,79 €
PAT123-30-250/SS	7	250	123	26	M30	23,5	288	20000	-	108,70 €

*Depending on availability - Dimensions in mm