
Conical flexible mount


PCF — Square base plate


- **With 4 fixing holes**
- Suspension mainly by axial spring action
- Materials:
  Centre: Natural rubber (60 Shore A)
  Support: steel




Uses

- Anti-vibration mounting support for motors and machines.







DISCOUNTS

Qty.	1+	6+	10+	20+	30+	50+
Disc.	List	-5%	-10%	-15%	-20%	On request

Part number	ØA	ØB	L	D	C1	C2	ØM	H	G	E	R	Price each 1 to 5
PCF4-16-78	16	78	107	90	80	65	11	56	19,5	3,5	R3	18,50 €
PCF4-16-93	16	93	120	100	90	74	11	81	20,0	4,3	R4	54,57 €
PCF4-20-109	20	109	140	120	112	92	11	95	23,0	4,5	R4	58,43 €

Our other products



Steel spur gear, Steel 20NCD2




Narrow spur rack, Stainless steel



Standard wire thimble, Steel



Crossed helical gear crossed axis at 90°, Steel 20NCD2



T type timing belt per metre, T5 Steel cored polyurethane



Bearing locknut, Self locking locknut - nylon lock washer



Stainless steel diabolo shaped elasto mount, Stainless steel



Female eye bolt conforms to DIN582, Steel



Worm and wheel gear reducer, up to 164 Nm



Articulated foot Ø103, Ø 103



Shoulder screw ISO7379, Hardened Steel class 12.9




Motor-gearbox 12V and 24V DC, from 1.5 to 2 Nm

Complementary products



Conical flexible mount, Oval base plate



Anti-vibration machine mount, Square base plate



Anti-vibration machine mount, Oval base plate