

Chain sprocket with **hardened teeth**

DIN06B-1 C45 tempered steel
3/8" 

- Pitch 9.525mm (DIN06B-1)
- Roller diameter 9.35
- Materials:
 C45 steel UNI7845
 Hardened teeth 45-53HRC

Accessory

- SBR-375/M chain


Info

- DIN 6885 keyway on the central tooth line
- Threaded hole on key and at 90°



Bore and keyway

2 threaded holes



DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part N°	Z Teeth	ØP	ØD	ØM	E	K			ØT	Price each
						ØA	(H9)	T2		1 to 5
PCS37-12H-12K	12	36,80	40,45	30	25	12	4	1,80	M4	5,64 €
14						5	2,30	M4	5,64 €	
15						5	2,30	M4	5,64 €	
16						5	2,30	M4	5,64 €	
PCS37-13H-12K	13	39,80	43,50	28	25	12	4	1,80	M4	6,09 €
14						5	2,30	M4	6,09 €	
15						5	2,30	M4	6,09 €	
16						5	2,30	M4	6,09 €	
PCS37-13H-18K	13	39,80	43,50	28	25	18	6	2,80	M5	6,09 €
12						4	1,80	M4	6,82 €	
14						5	2,30	M4	6,82 €	
15						5	2,30	M4	6,82 €	
PCS37-14H-12K	14	42,80	46,50	31	25	12	4	1,80	M4	6,82 €
14						5	2,30	M4	6,82 €	
15						5	2,30	M4	6,82 €	
16						5	2,30	M4	6,82 €	
PCS37-14H-18K	14	42,80	46,50	31	25	18	6	2,80	M5	6,82 €

All dimensions in mm

Part N°	Z					K				Price each 1 to 5
	Teeth	ØP	ØD	ØM	E	ØA	(H9)	T2	ØT	
PCS37-15H-14K						14	5	2,30	M4	6,94 €
PCS37-15H-15K						15	5	2,30	M4	6,94 €
PCS37-15H-16K						16	5	2,30	M4	6,94 €
PCS37-15H-18K	15	45,81	49,50	34	25	18	6	2,80	M4	6,94 €
PCS37-15H-19K						19	6	2,80	M5	6,94 €
PCS37-15H-20K						20	6	2,80	M5	6,94 €
PCS37-15H-22K						22	6	2,80	M5	6,94 €
PCS37-15H-24K						24	8	3,30	M6	6,94 €
PCS37-16H-14K										
PCS37-16H-15K						15	5	2,30	M4	7,44 €
PCS37-16H-16K						16	5	2,30	M4	7,44 €
PCS37-16H-18K	16	48,82	52,30	37	28	18	6	2,80	M5	7,44 €
PCS37-16H-19K						19	6	2,80	M5	7,44 €
PCS37-16H-20K						20	6	2,80	M5	7,44 €
PCS37-16H-22K						22	6	2,80	M5	7,44 €
PCS37-16H-24K						24	8	3,30	M6	7,44 €
PCS37-17H-14K										
PCS37-17H-15K						15	5	2,30	M4	7,88 €
PCS37-17H-16K						16	5	2,30	M4	7,88 €
PCS37-17H-18K	17	51,83	55,50	40	28	18	6	2,80	M5	7,88 €
PCS37-17H-19K						19	6	2,80	M5	7,88 €
PCS37-17H-20K						20	6	2,80	M5	7,88 €
PCS37-17H-22K						22	6	2,80	M5	7,88 €
PCS37-17H-24K						24	8	3,30	M6	7,88 €
PCS37-18H-14K										
PCS37-18H-15K						15	5	2,30	M4	8,01 €
PCS37-18H-16K						16	5	2,30	M4	8,01 €
PCS37-18H-18K	18	54,85	58,30	43	28	18	6	2,80	M5	8,01 €
PCS37-18H-19K						19	6	2,80	M5	8,01 €
PCS37-18H-20K						20	6	2,80	M5	8,01 €
PCS37-18H-22K						22	6	2,80	M5	8,01 €
PCS37-18H-24K						24	8	3,30	M6	8,01 €
PCS37-19H-15K										
PCS37-19H-16K						16	5	2,30	M4	8,70 €
PCS37-19H-18K						18	6	2,80	M5	8,70 €
PCS37-19H-19K	19	57,87	61,60	45	28	19	6	2,80	M5	8,70 €
PCS37-19H-20K						20	6	2,80	M5	8,70 €
PCS37-19H-22K						22	6	2,80	M5	8,70 €
PCS37-19H-24K						24	8	3,30	M6	8,70 €
PCS37-19H-25K						25	8	3,30	M6	8,70 €
PCS37-20H-15K										
PCS37-20H-16K						16	5	2,30	M4	9,23 €
PCS37-20H-18K						18	6	2,80	M5	9,23 €
PCS37-20H-19K	20	60,89	64,30	46	28	19	6	2,80	M5	9,23 €
PCS37-20H-20K						20	6	2,80	M5	9,23 €
PCS37-20H-22K						22	6	2,80	M5	9,23 €
PCS37-20H-24K						24	8	3,30	M6	9,23 €
PCS37-20H-25K						25	8	3,30	M6	9,23 €

Chain sprocket with **hardened teeth**

DIN06B-1  **C45 tempered steel**
3/8"

- Pitch 9.525mm (DIN06B-1)
- Roller diameter 9.35
- Materials:
 C45 steel UNI7845
 Hardened teeth 45-53HRC

Accessory

- SBR-375/M chain

Info

- DIN 6885 keyway on the central tooth line
- Threaded hole on key and at 90°



Bore and keyway

2 threaded holes


DISCOUNTS

Qty	1+	6+	20+	40+
Disc.				
List	-12%	-25%		On request



Part N°	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Price each 1 to 5
PCS37-21H-15K						15	5	2,30	M4	9,52 €
PCS37-21H-16K						16	5	2,30	M4	9,52 €
PCS37-21H-18K						18	6	2,80	M5	9,52 €
PCS37-21H-19K	21	63,91	67,60	48	28	19	6	2,80	M5	9,52 €
PCS37-21H-20K						20	6	2,80	M5	9,52 €
PCS37-21H-22K						22	6	2,80	M5	9,52 €
PCS37-21H-24K						24	8	3,30	M6	9,52 €
PCS37-21H-25K						25	8	3,30	M6	9,52 €
PCS37-23H-15K										
PCS37-23H-16K						16	5	2,30	M4	11,40 €
PCS37-23H-18K						18	6	2,80	M5	11,40 €
PCS37-23H-19K	23	69,95	73,70	52	28	19	6	2,80	M5	11,40 €
PCS37-23H-20K						20	6	2,80	M5	11,40 €
PCS37-23H-22K						22	6	2,80	M5	11,40 €
PCS37-23H-24K						24	8	3,30	M6	11,40 €
PCS37-23H-25K						25	8	3,30	M6	11,40 €

All dimensions in mm



DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part N°	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Price each					
										1 to 5					
PCS37-24H-18K	24	72,97	76,70	54	28	18	6	2,80	M5	12,22 €					
PCS37-24H-19K						19	6	2,80	M5	12,22 €					
PCS37-24H-20K						20	6	2,80	M5	12,22 €					
PCS37-24H-22K						22	6	2,80	M5	12,22 €					
PCS37-24H-24K						24	8	3,30	M6	12,22 €					
PCS37-24H-25K						25	8	3,30	M6	12,22 €					
PCS37-24H-28K						28	8	3,30	M6	12,22 €					
PCS37-24H-30K						30	8	3,30	M6	12,22 €					
PCS37-25H-18K						25	76,00	79,70	57	28	18	6	2,80	M5	13,12 €
PCS37-25H-19K											19	6	2,80	M5	13,12 €
PCS37-25H-20K	20	6	2,80	M5	13,12 €										
PCS37-25H-22K	22	6	2,80	M5	13,12 €										
PCS37-25H-24K	24	8	3,30	M6	13,12 €										
PCS37-25H-25K	25	8	3,30	M6	13,12 €										
PCS37-25H-28K	28	8	3,30	M6	13,12 €										
PCS37-25H-30K	30	8	3,30	M6	13,12 €										
PCS37-27H-20K	27	82,05	85,70	60	28						20	6	2,80	M5	15,65 €
PCS37-27H-22K											22	6	2,80	M5	15,65 €
PCS37-27H-24K						24	8	3,30	M6	15,65 €					
PCS37-27H-25K						25	8	3,30	M6	15,65 €					
PCS37-27H-28K						28	8	3,30	M6	15,65 €					
PCS37-27H-30K						30	8	3,30	M6	15,65 €					
PCS37-30H-20K	30	91,12	94,80	60	30	20	6	2,80	M5	18,19 €					
PCS37-30H-22K						22	6	2,80	M5	18,19 €					
PCS37-30H-24K						24	8	3,30	M6	18,19 €					
PCS37-30H-25K						25	8	3,30	M6	18,19 €					
PCS37-30H-28K						28	8	3,30	M6	18,19 €					
PCS37-30H-30K						30	8	3,30	M6	18,19 €					

Our other products



MSP23

Masterplate® glueable insert Ø23, Cylindrical Ø23 with threaded s...



GAL48_OMNI

Omni-directional roller, Omni-directional



PFC

Fixed rubber levelling foot, Levelling support for small parts



T10-BAR

T type tooth bar stock, T10



RJUM05

Drylin R® linear bearing housing, Closed - Long



G4

Steel spur gear, Steel 20NCD2



CHA135

Screwed hinge, 135 degrees



BAC105

Storage bin, 8mm



CHASb63

Hinge without pin, Polymer pin hinge



BMM

Knurled knob - male, Knurled



ZBconique

Machined plastic bevel gear, 1:1



UGH50

H Type Guide units, For Ø50 actuators

Complementary products



SUA4

Single chain supplied by the metre, Steel



SUA4_L

Chain link, Steel



PCS37

Chain sprocket - steel, 9.525mm (DIN06B-1)



PCS_PA6

Plastic sprocket, 9.525mm (DIN 06B-1)