
Chain sprocket with hardened teeth Ste DIN

DIN10B-1 — C45 tempered steel

5/8”



- **Pitch 15,875mm (DIN 10B-1)**
- Roller diameter 10,16mm
- Materials:
  C45 steel UNI7845
  Hardened teeth 45-53HRC




Accessory

- **SBR-625/M** chain

Info

- DIN 6885 keyway on the central tooth line
- Threaded hole on key and at 90°



DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part N°	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Price each 1 to 5
PCS62-12H-16K	12	61,34	68,20	42	30	16	5	2,30	M4	10,66 €
PCS62-12H-19K						19	6	2,80	M5	10,66 €
PCS62-12H-20K						20	6	2,80	M5	10,66 €
PCS62-12H-22K						22	6	2,80	M5	10,66 €
PCS62-12H-24K						24	8	3,30	M6	10,66 €
PCS62-12H-25K						25	8	3,30	M6	10,66 €
PCS62-12H-28K				51	30	28	8	3,30	M6	10,66 €
PCS62-12H-30K				51	30	30	8	3,30	M6	10,66 €
PCS62-13H-16K	13	66,32	73,20	47	30	16	5	2,30	M4	11,40 €
PCS62-13H-19K						19	6	2,80	M5	11,40 €
PCS62-13H-20K						20	6	2,80	M5	11,40 €
PCS62-13H-22K						22	6	2,80	M5	11,40 €
PCS62-13H-24K						24	8	3,30	M6	11,40 €
PCS62-13H-25K						25	8	3,30	M6	11,40 €
PCS62-13H-28K						28	8	3,30	M6	11,40 €
PCS62-13H-30K						30	8	3,30	M6	11,40 €

All dimensions in mm

DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part N°	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Price each 1 à 5
PCS62-14H-16K	14	71,34	78,20	52	30	16	5	2,30	M4	12,26 €
PCS62-14H-19K						19	6	2,80	M5	12,26 €
PCS62-14H-20K						20	6	2,80	M5	12,26 €
PCS62-14H-22K						22	6	2,80	M5	12,26 €
PCS62-14H-24K						24	8	3,30	M6	12,26 €
PCS62-14H-25K						25	8	3,30	M6	12,26 €
PCS62-14H-28K						28	8	3,30	M6	12,26 €
PCS62-14H-30K						30	8	3,30	M6	12,26 €
PCS62-15H-19K	15	76,36	83,20	57	30	19	6	2,80	M5	13,73 €
PCS62-15H-20K						20	6	2,80	M5	13,73 €
PCS62-15H-22K						22	6	2,80	M5	13,73 €
PCS62-15H-24K						24	8	3,30	M6	13,73 €
PCS62-15H-25K						25	8	3,30	M6	13,73 €
PCS62-15H-28K						28	8	3,30	M6	13,73 €
PCS62-15H-30K						30	8	3,30	M6	13,73 €
PCS62-15H-32K						32	10	3,30	M8	13,73 €
PCS62-15H-35K						35	10	3,30	M8	13,73 €
PCS62-16H-20K	16	81,37	88,00	60	30	20	6	2,80	M5	14,55 €
PCS62-16H-22K						22	6	2,80	M5	14,55 €
PCS62-16H-24K						24	8	3,30	M6	14,55 €
PCS62-16H-25K						25	8	3,30	M6	14,55 €
PCS62-16H-28K						28	8	3,30	M6	14,55 €
PCS62-16H-30K						30	8	3,30	M6	14,55 €
PCS62-16H-32K						32	10	3,30	M8	14,55 €
PCS62-16H-35K						35	10	3,30	M8	14,55 €
PCS62-17H-20K	17	86,39	93,20	60	30	20	6	2,80	M5	15,90 €
PCS62-17H-22K						22	6	2,80	M5	15,90 €
PCS62-17H-24K						24	8	3,30	M6	15,90 €
PCS62-17H-25K						25	8	3,30	M6	15,90 €
PCS62-17H-28K						28	8	3,30	M6	15,90 €
PCS62-17H-30K						30	8	3,30	M6	15,90 €
PCS62-17H-32K						32	10	3,30	M8	15,90 €
PCS62-17H-35K						35	10	3,30	M8	15,90 €
PCS62-18H-20K	18	91,42	98,30	70	30	20	6	2,80	M5	17,70 €
PCS62-18H-22K						22	6	2,80	M5	17,70 €
PCS62-18H-24K						24	8	3,30	M6	17,70 €
PCS62-18H-25K						25	8	3,30	M6	17,70 €
PCS62-18H-28K						28	8	3,30	M6	17,70 €
PCS62-18H-30K						30	8	3,30	M6	17,70 €
PCS62-18H-32K						32	10	3,30	M8	17,70 €
PCS62-18H-35K						35	10	3,30	M8	17,70 €
PCS62-18H-38K						38	10	3,30	M8	17,70 €
PCS62-18H-40K						40	12	3,30	M10	17,70 €


Chain sprocket with hardened teeth Ste DIN

DIN10B-1 — C45 tempered steel

5/8”



- **Pitch 15,875mm (DIN 10B-1)**
- Roller diameter 10,16mm
- Materials:
  C45 steel UNI7845
  Hardened teeth 45-53HRC




Accessory

- **SBR-625/M** chain

Info

- DIN 6885 keyway on the central tooth line
- Threaded hole on key and at 90°



DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part N°	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Price each 1 to 5
PCS62-19H-20K	19	96,45	103,30	70	30	20	6	2,80	M5	19,13 €
PCS62-19H-22K						22	6	2,80	M5	19,13 €
PCS62-19H-24K						24	8	3,30	M6	19,13 €
PCS62-19H-25K						25	8	3,30	M6	19,13 €
PCS62-19H-28K						28	8	3,30	M6	19,13 €
PCS62-19H-30K						30	8	3,30	M6	19,13 €
PCS62-19H-32K						32	10	3,30	M8	19,13 €
PCS62-19H-35K						35	10	3,30	M8	19,13 €
PCS62-19H-38K						38	10	3,30	M8	19,13 €
PCS62-19H-40K						40	12	3,30	M10	19,13 €

All dimensions in mm

Part N°	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Price each 1 to 5
PCS62-20H-20K						20	6	2,80	M5	21,09 €
PCS62-20H-22K						22	6	2,80	M5	21,09 €
PCS62-20H-24K						24	8	3,30	M6	21,09 €
PCS62-20H-25K						25	8	3,30	M6	21,09 €
PCS62-20H-28K						28	8	3,30	M6	21,09 €
PCS62-20H-30K	20	101,49	108,40	75	30	30	8	3,30	M6	21,09 €
PCS62-20H-32K						32	10	3,30	M8	21,09 €
PCS62-20H-35K						35	10	3,30	M8	21,09 €
PCS62-20H-38K						38	10	3,30	M8	21,09 €
PCS62-20H-40K						40	12	3,30	M10	21,09 €
PCS62-21H-20K						20	6	2,80	M5	22,27 €
PCS62-21H-22K						22	6	2,80	M5	22,27 €
PCS62-21H-24K						24	8	3,30	M6	22,27 €
PCS62-21H-25K						25	8	3,30	M6	22,27 €
PCS62-21H-28K						28	8	3,30	M6	22,27 €
PCS62-21H-30K	21	106,52	113,40	75	30	30	8	3,30	M6	22,27 €
PCS62-21H-32K						32	10	3,30	M8	22,27 €
PCS62-21H-35K						35	10	3,30	M8	22,27 €
PCS62-21H-38K						38	10	3,30	M8	22,27 €
PCS62-21H-40K						40	12	3,30	M10	22,27 €
PCS62-23H-20K						20	6	2,80	M5	25,46 €
PCS62-23H-22K						22	6	2,80	M5	25,46 €
PCS62-23H-24K						24	8	3,30	M6	25,46 €
PCS62-23H-25K						25	8	3,30	M6	25,46 €
PCS62-23H-28K						28	8	3,30	M6	25,46 €
PCS62-23H-30K	23	116,58	123,40	80	30	30	8	3,30	M6	25,46 €
PCS62-23H-32K						32	10	3,30	M8	25,46 €
PCS62-23H-35K						35	10	3,30	M8	25,46 €
PCS62-23H-38K						38	10	3,30	M8	25,46 €
PCS62-23H-40K						40	12	3,30	M10	25,46 €
PCS62-23H-42K						42	12	3,30	M10	25,46 €
PCS62-24H-20K						20	6	2,80	M5	26,77 €
PCS62-24H-22K						22	6	2,80	M5	26,77 €
PCS62-24H-24K						24	8	3,30	M6	26,77 €
PCS62-24H-25K						25	8	3,30	M6	26,77 €
PCS62-24H-28K						28	8	3,30	M6	26,77 €
PCS62-24H-30K	24	121,62	128,50	80	30	30	8	3,30	M6	26,77 €
PCS62-24H-32K						32	10	3,30	M8	26,77 €
PCS62-24H-35K						35	10	3,30	M8	26,77 €
PCS62-24H-38K						38	10	3,30	M8	26,77 €
PCS62-24H-40K						40	12	3,30	M10	26,77 €
PCS62-24H-42K						42	12	3,30	M10	26,77 €
PCS62-25H-22K						22	6	2,80	M5	27,71 €
PCS62-25H-24K						24	8	3,30	M6	27,71 €
PCS62-25H-25K						25	8	3,30	M6	27,71 €
PCS62-25H-28K						28	8	3,30	M6	27,71 €
PCS62-25H-30K	25	126,66	133,50	80	30	30	8	3,30	M6	27,71 €
PCS62-25H-32K						32	10	3,30	M8	27,71 €
PCS62-25H-35K						35	10	3,30	M8	27,71 €
PCS62-25H-38K						38	10	3,30	M8	27,71 €
PCS62-25H-40K						40	12	3,30	M10	27,71 €
PCS62-25H-42K						42	12	3,30	M10	27,71 €

Our other products


AC

Strike for toggle latch, 18mm


SVT5

Screwjack with travelling screw, with translating screw


HAS

Captive C washer, Slotted flat headed shoulder screw


ERC

Quick fitting cable terminal, Fork


HRV

V- rail guidance Simple Select® system, Rail with carriage


CHT

Asynchronous AC Motor, 0.55 to 1.1kW


RJABLU

Sealing strip, approved


CHA1056-U4

Screwed hinge, 180°


ES

Bipod support base, Plastic


VQT

Quarter-turn clamp lock, Plastic or stainless steel button



WJRM

Drylin® W hybrid bearing block, Hybrid bearings


PSG2S

Spur gear - precision range, Stainless steel 303

Complementary products


SUA4

Single chain supplied by the metre, Steel


SUA4_L

Chain link, Steel


PCS62

Chain sprocket - steel, 15.875 (DIN 10B-1)


PCS62SS

Chain sprocket - Stainless steel, 15.875mm (DIN 08B-1)