

Handle



PHT For use in high temperatures up to 250°C

- **Heavy-duty handle, resists high temperatures**
- Working temperature:
Continuous operation: max + 150/160°C
Occasional use: + 250°C max
- Material:
Thermoplastic PPA, glass-fibre reinforced,
black finish



Applications

- Ovens
- Machines generating heat

Mounting


- The mounting hole allows the handle to be secured with either a cylindrical or hexagonal headed screw.
- Front or rear mounting



150°C
Continuously



250°C
For short periods



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	Net	-5%	-15%	On request

Part N°	A	B	C	ØD	H	L	L1	SW	T	T1	Load (N)	Price each
												1 to 5
PHT-117	117	26	10	9	41	136	94	13	15	8	1500	8,11 €
PHT-132	132	27	11	9	44	154	112	13	16	8	1500	12,87 €

All dimensions in mm



Handle

For use in high temperatures up to 250°C PHT_{SS}

- **Heavy-duty handle, resists high temperatures**
- Working temperature:
 - Continuous operation: max + 150/160°C
 - Occasional use: + 250°C max
- Material:
 - Thermoplastic PPA, glass-fibre reinforced, black finish
 - Threaded insert: stainless steel

Applications

- This handle is larger than most and has an ergonomic design.
- Easy to clean thanks to a closed and smooth design.
- For use in the food or medical industries.

Mounting



- Rear mounting



150°C
Continuously



250°C
For short periods




DISCOUNTS

Qty	1+	6+	20+	50+
Disc. Net	-5%	-15%	On request	

Part N°	A	B	C	ØD	H	L	S	T	Charge (N)	Price each
										1 to 5
PHT-100/SS	100	17	10,3	M5	34,0	122,5	20	9	1000	17,25 €
PHT-120/SS	120	21	12,4	M6	41,0	146,0	24	12	1000	20,68 €
PHT-140/SS	140	24	15,4	M8	46,5	170,0	28	12	1000	28,46 €

All dimensions in mm

Our other products



LSM

Stainless steel 316L
leadscrew, Stainless
steel - 1 thread



CHAE4080PA

Symmetrical decorative
screwed hinge,
Polyamide



DCA

Suction cup, 1.5
bellows, nitrile



VAB

Flanged nut for ball
screw, For VAB
ballscrew



BPHR

Ball transfer unit
housed spring loaded,
High



GLT3-46A

Telescopic drawer
with damper,



SH0

Parallel axis helical
gear, Machined plastic
(delrin)



WJUM10

Drylin® W bearing
block, Slide



HBM

Adjustment bushing
for half-rail guide,



DOG258

Motor-gearbox 12V
and 24V DC, from 12



RBNpl

Swivel castor with
double brake, Steel -



GG2

Ground spur gear,
Heat treated steel

Complementary products



PO

Pull handle - Multi-
sector, Tapped
recessed insert



PGM52-M4

Pull handle,
Aluminium



PGMT

Pull handle, Steel



PGM52-M4

Pull handle, Brass