


Cylindrical magnet

SmCo

PLM

- **Smooth finish, shielded system**
- Do not press fit directly into an iron support as a magnetic short circuit will reduce the adhesive force
- Suitable for use in spot welding machines.
- Dimension "H" can be reduced with no loss of adhesive force
- Max working temp : +200°C
- **Material, finish**
Galvanised steel body,
Magnetic core SmCo



INCREASED STOCK

DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-15%	-20%	-30%	On request



Part number	ØD	L	H	Attraction force (N)	Distance to iron wall/mm	Weight (g)	Stock*	Price each 1 to 5
PLM6-20/SC	6	20	10,0	8	1,5	4,5	✓	6,44 €
PLM8-20/SC	8	20	10,0	22	1,5	8,0	✓	8,11 €
PLM10-20/SC	10	20	8,0	40	2,0	12,0	✓	9,94 €
PLM13-20/SC	13	20	6,0	60	2,5	20,0	-	13,18 €
PLM16-20/SC	16	20	2,0	125	3,0	30,0	-	17,95 €
PLM20-25/SC	20	25	5,0	250	4,0	60,0	-	29,36 €
PLM25-35/SC	25	35	7,0	400	5,0	134,0	-	66,14 €
PLM32-40/SC	32	40	4,5	600	6,0	251,0	-	120,64 €

Threaded cylindrical magnet

NdFeB

PLM

- **Shielded system**
- Suitable for mounting in steel or iron supports
- Can also be used as blind-hole magnets
- Max working temp : +80°C
- **Material, finish**
Galvanised steel body,
Magnetic core NdFeB



DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-15%	-20%	-30%	On request

Part number	ØD	ØD1	L	T	Attraction force (N)	Weight (g)	Stock*	Price each 1 to 5
PLM8-12/N	8	M3	12	5	12	7	✓	7,49 €
PLM10-16/N	10	M4	16	7	24	8	✓	8,59 €
PLM13-18/N	13	M4	18	7	60	18	✓	9,82 €
PLM16-20/N	16	M4	20	7	90	30	✓	10,42 €
PLM20-25/N	20	M5	25	9	135	60	-	18,02 €
PLM25-30/N	25	M6	30	9	190	110	-	38,44 €
PLM35-40/N	35	M8	40	13	300	290	-	66,50 €

Dimensions in mm

Our other products



CDGamme

Compression spring,
DIN 2095



DOMI50

DOMILINE -
Accessories, Plate



HW_HT

Half-rail guide, Rail



CHMX_CHMDX

double output shafts,
CHMR and CHM
gearboxes double
sided output shaft



PTA80

Articulated levelling
foot, pressed base
Ø80, Ø 80



GLT16

Mini telescopic 3 part
slide, Miniature



NT92

Spur gear coaxial
gearbox, from 15 to
40 Nm - In-line




D-PAR_SS

Progressive stop,
stainless steel



GSI

Gas spring, Stainless
steel



GMK17_P

Flat Guides, Flat guide
for conical profile



MEB-ALI

Moulded plastic bevel
gear (blue nylon), 1:1



GP

Spring loaded toggle
latch, With padlock-
holder

Complementary products



PLM-C

Cylindrical holding
magnets, Cylindrical
holding magnet



PLM-20SC

Threaded cylindrical
magnet, With
threaded hole