


Cylindrical holding magnets



PLM AINiCo, calibrated external diameter

- Cylindrical gripping magnet
- Shielded system
- Fixed used a press, shrink fitting or adhesive
- Dimension "H" can be reduced without affecting adhesive force
- Max working temp : 450°C
- **Material, finish**
Galvanised steel body,
Magnetic core AINiCo



DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-15%	-20%	-30%	On request


Part number	ØD	L	H	Attraction force (N)	Weight (g)	Stock*	Price each. 1 to 5
PLM6-10/C	6	10	2	1,5	2	✓	5,30 €
PLM8-12/C	8	12	3	3,5	4	✓	5,76 €
PLM10-16/C	10	16	6	7,0	9	✓	6,16 €
PLM13-18/C	13	18	7	10,0	17	-	6,97 €
PLM16-20/C	16	20	5	18,0	29	-	8,84 €
PLM20-25/C	20	25	6	42,0	57	-	11,86 €
PLM25-30/C	25	30	5	96,0	110	-	20,87 €
PLM32-35/C	32	35	3	180,0	200	-	34,90 €
PLM40-45/C	40	45	5	240,0	420	-	78,33 €
PLM50-50/C	50	50	2	420,0	720	-	152,52 €

Flat gripping magnet

PLM

Hard ferrite core

- Flat magnet without a threaded core
- Shielded system
- These holding magnets can be force fitted or glued into positioning holes
- Max working temp : +200°C
- **Material, finish**
Galvanised steel body,
Hard ferrite magnetic core



DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-15%	-20%	-30%	On request



Part number	ØD	L	Attraction force (N)	Weight (g)	Stock*	Price each. 1 to 5
PLM10-4/P	10 ^{±0,15}	4,5	4	2,0	✓	2,33 €
PLM13-4/P	13 ^{±0,15}	4,5	10	3,0	✓	2,62 €
PLM16-4/P	16 ^{±0,15}	4,5	18	4,5	-	3,10 €
PLM20-6/P	20 ^{±0,15}	6,0	30	10,0	✓	3,76 €
PLM25-7/P	25 ^{±0,15}	7,0	40	19,0	✓	4,12 €
PLM32-7/P	32 ^{±0,20}	7,0	80	30,0	✓	4,46 €
PLM40-8/P	40 ^{±0,20}	8,0	125	55,0	-	6,04 €
PLM50-10/P	50 ^{±0,20}	10,0	220	100,0	-	7,61 €
PLM63-14/P	63 ^{±0,20}	14,0	350	230,0	✓	13,36 €

Dimensions in mm


Our other products



BMM
Knob for clamping,
Knurled



PRFSRAD
Closing system, Quick
fitting, self locking
door dual lock



POA
Magnetic workshop
tool support, Magnetic
bar



H0
90° crossed axis
helical gear, Steel
20NCD2



CHA_GC_9SS
Hinge (stainless
steel), To be welded



AXTR
Tensioner pulley,
Shaft



SR
Rack, rectangular
section, Stainless
steel



MDB_MTB
Moulded plastic bevel
gear (nylon), 2:1



HD
Universal joint - steel,
Needle bearings -
double



NIN
Self locking nut - DIN
985, Steel



BGC
Oldham, Clamp



GMK17_RG
Clip for guide,
Rounded

Complementary products



PLM-SC
Magnetic stud, With
threaded hole



PLM-SC
Magnetic stud, With
milled bore