
Idler sprocket for plate chain

For chain ranges 821 and 805 — PR821

- ***For use with CAP821 and CAP805 plate chains***
- *Materials:*
  Reinforced polyamide
  Stainless steel screws
- *Operating temp.: -10°C to +120°C*
- *For dimensions and bore tolerances, please refer to technical pages*




Advantage

- *Two part design facilitates easy assembly*

Easy assembly



Two part design



DISCOUNTS

Qty.	1+	5+	10+
Disc.	List	-5%	On request

Part number	No. of teeth	ØDE	ØDP	Bore ØA	Weight (kg)	Price each 1 to 4
PR821-25-30	25	153	153,2	30	0,9	70,12 €
PR821-25-35	25	153	153,2	35	0,9	70,12 €
PR821-25-40	25	153	153,2	40	0,9	70,12 €
PR821-25-45	25	153	153,2	45	0,9	70,12 €

Dimensions in mm

Our other products



SCE

U-shaped cable clamp, Steel



SSDB

Stainless steel bevel gear, 2:1



GAL21

Conveyor wheel, Plastic



CHTRP

Single and dual output gearboxes, Up to 28,8 Nm



PRS80

Stainless steel articulated foot Ø80, Ø 80



DOMI80

Accessories, Plate



JCSss

Single stainless steel universal joint, Low duty



G-ECO

Eco range Spur gear, Steel C45



AC

Strike for toggle latch, 15mm



PRF_ECL

Nut for aluminium profile, Steel square nut with tab



TCXR

Automatic chain tensioner, With stainless steel



DBL820

Idler for slat top chain, Ranges 820 and 815

Complementary products