Idler sprocket for plate chain

PR882


For chain range 882 TAB

- ***For use with CAP882T plate chains***
- *Materials:*
  Reinforced polyamide
  Stainless steel screws
- *Operating temp.: -10°C to +120°C*
- *For dimensions and bore tolerances, please refer to technical pages*

Advantage


- *Two part design facilitates easy assembly*

Easy assembly





Two part design



DISCOUNTS

Qty.	1+	5+	10+
Disc.	List	-5%	On request

Part number	No. of teeth	ØDE	ØDP	Bore ØA	Weight (kg)	Price each 1 to 4
PR882-12-25	12	148,5	147,2	25	0,38	29,36 €
PR882-12-30	12	148,5	147,2	30	0,38	29,36 €
PR882-12-35	12	148,5	147,2	35	0,38	29,36 €
PR882-12-40	12	148,5	147,2	40	0,38	29,36 €
PR882-12-45	12	148,5	147,2	45	0,38	29,36 €

Dimensions in mm


Our other products




Conical elasto buffer, Stainless steel



Right angled gearbox, double output shafts, up to 10.3 Nm



Hinge and joint, Lift-off hinge



1A motorised linear actuator, 1 ampere



Extension spring in metre length stainless steel, by the metre



Plastic spur gear, Machined plastic (delrin)




Indexing plunger, stainless steel



High rigidity linear slide, Rail - from 9320 N to 71300 N



Connecting plate for RPP type timing belts,



Manual lifting tables, 20kg



Connecting plate for RPP type timing belts,



Half-rail guide, Wheel

Complementary products



Flexible slat top chain acetal, Large range 882



Drive sprocket for slat top chain, Range 882