

Manual workbench press



PRES2HR

Force up to 200 kg


- Rack press
- The force is linear and constant over the full stroke.
- The ram is prevented from turning
- Free height is adjustable
- Stroke adjusts via a screw
- Quick and easy to install

Applications

- This model is particularly robust and is frequently used for the assembly of parts, simple bending tasks and various fastening operations

Option

- None available



DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Force (kg)	Free height HL (mm)	Stroke (mm)	Goose neck depth (mm)	Weight (kg)	Stock*	Price each
PRES-2HR	200	54 - 200	50	72	8	✓	672,26 €

*Depending on availability - Dimensions in mm



Manual workbench press

Force up to **400 kg**

PRES3HR

- Rack press
- The force is linear and constant over the full stroke.
- The ram is prevented from turning
- Free height is adjustable
- Stroke adjusts via a screw
- Quick and easy to install

Applications


- This model is particularly robust and is frequently used for the assembly of parts, simple bending tasks and various fastening operations

Options

- 5 digit counter with reset button
- Accessories- see accessory page (tome 5 p.21)



version with counter



DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Force (kg)	Free height HL (mm)	Stroke (mm)	Goose neck depth (mm)	Weight (kg)	Counter	Stock*	Price each
PRES-3HR	400	35 - 270	80	80	17	Without	✓	1 069,70 €
PRES-3HR-CPT	400	35 - 270	80	80	17	With	-	1 454,33 €

*Depending on availability - Dimensions in mm

Manual workbench press



PRES4HR

Force up to 600 kg

- Rack press
- The force is linear and constant over the full stroke.
- The ram is prevented from turning
- Free height is adjustable
- Stroke adjusts via a screw
- Quick and easy to install

Applications


- This model is particularly robust and is frequently used for the assembly of parts, simple bending tasks and various fastening operations

Options

- 5 digit counter with reset button
- Accessories- see accessory page (tome 5 p.21)



version with counter



DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Power (kg)	Free height HL (mm)	Stroke (mm)	Goose neck depth (mm)	Weight (kg)	Counter	Price each
PRES-4HR	600	46 - 280	100	95	25	Without	1 189,91 €
PRES-4HR-CPT	600	46 - 280	100	95	25	With	1 574,51 €

Dimensions in mm



Manual bench press


500 kg capacity

PRES5HR

- **Knee-joint press**
- The maximum power is reached at the end of the stroke
- The travelling nut is prevented from turning
- Adjustable free height
- Screw stroke adjustment
- Quick and easy installation

Uses

- This model is particularly robust and is normally used for the assembly of parts, simple bending tasks and various fastening operations



DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Power (kg)	Free height HL (mm)	Stroke length (mm)	Goose neck depth (mm)	Weight (kg)	Stock*	Price each
PRES-5HR	500	42 - 185	50	72	9	✓	605.97 €

*Depending on availability - Dimensions in mm

Manual bench press




PRES7HR

700 kg capacity

- **Knee-joint press**
- The maximum power is reached at the end of the stroke
- The travelling nut is prevented from turning
- Adjustable free height
- Screw stroke adjustment
- Quick and easy installation

Uses

- This model is particularly robust and is normally used for the assembly of parts, simple bending tasks and various fastening operations



DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Power (kg)	Free height HL (mm)	Stroke length (mm)	Goose neck depth (mm)	Weight (kg)	Price each
PRES-7HR	700	35 - 260	40	95	25	1 244,00 €

Dimensions in mm

Manual workbench press

Accessories for PRES-3HR and PRES-4HR presses

PRES

These accessories are only suitable for use with the PRES-3HR and PRES-4HR presses

PRES-PMB: Micrometric adjustment PMB.
Bottom dead centre adjustment system, graduated every 0.02 mm

PRES-TE: Slot nuts for securing tools in the T slot

PRES-ER25: Collet chuck
Collet chuck with ER25 collet for shanks from \varnothing 1.5 to \varnothing 16 mm (Other diameters between 1.5 and 16 mm available on request)



PRES-PMB



PRES-TE



PRES-ER25

DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Type	For shank diameter	Price each
PRES-PMB	Micrometric adjustment (0.02mm)	-	502,59 €
PRES-TE	Set of slot nuts for T profile slots	-	41,66 €
PRES-ER25-1.5	tool holder	1,5	450,30 €
PRES-ER25-2	tool holder	2	450,30 €
PRES-ER25-4	tool holder	4	450,30 €
PRES-ER25-6	tool holder	6	450,30 €
PRES-ER25-8	tool holder	8	450,30 €
PRES-ER25-10	tool holder	10	450,30 €
PRES-ER25-12	tool holder	12	450,30 €
PRES-ER25-14	tool holder	14	450,30 €
PRES-ER25-16	tool holder	16	450,30 €

Dimensions in mm