Magnetic lock for aluminium profile

Easily adjustable lock

PRF*SMA*

- ***Lock for sliding doors on systems assembled using PRF454545 aluminium profiles***
- *Material:*
  Handle - glass-fibre reinforced PA6
  Magnet - Neodymium
  Magnet - stainless steel
  Back plate - galvanised steel




Advantages

- *Easy front-mounting of the handle using M6 CHC screws and the counter plate using M5 FHC screws*
- *No drilling required*

Accessories

- **CHC6-16** *screws and* **PRF-ECL-M6** *square nut, not provided*
- **FHC5-12** *screws and* **PRF-ECL-M5** *square nut, not provided*



DISCOUNTS

Qty	1+	2+	5+
Disc.	Net	-5%	On request

Part N°	C	D	Holding force (N)	Weight (g)	Price each
PRF-SMA-102	30	38, 1.5" 40, 45, 50, 60	25	168	23,78 €
	40	38, 1.5" 40, 45, 50, 60			
	45	38, 1.5" 40, 45, 50			
	50	38, 1.5" 40, 45, 50			
	60	30, 38, 1.5" 40, 45			

All dimensions in mm

Our other products



BH02

Single housed bearing assembly, Bearing secured with circlips



CHTRP

Single and dual output gearboxes, Up to 75,7 Nm



RVM25

Manually operated gearbox, Bevel



Q3

Double row angular contact ball bearing, Angular contact - Steel



PSG08S

Spur gear - precision range, Stainless steel 303



G-ECO15

Eco range Spur gear, Steel C45



ZBconique

Machined plastic bevel gear, 1:1



SHNbr

Hexagonal nut DIN934, Brass



CXS

External circlip DIN471, external DIN 471



E15

Right angle helical reducers, from 0.40 to 2.53 Nm



PFC

Fixed rubber levelling foot, Levelling support for small parts



BPHRF

Ball transfer unit housed spring loaded, High

Complementary products



CHC

Socket headed screw, Steel class 12.19



PRF_ECL_

Nut for aluminium profile, Steel square nut with tab



FHCSS

Countersunk screw, Stainless steel A2 - DIN 7991



PRF4545

Standard aluminium profile, 45 x 45 mm