

Our other products



T5P_T10P
Connecting plate for T type timing belts, T10



CHM63
Worm and wheel gear reducer, up to 196 Nm



STRIP1000
Sealing brush strip, 1m length



GE
Toggle latches, Miniature



CHM63-MOT
Asynchronous AC motorgearboxes 0.37 to 1.5kW, 0.37 to 1.5kW



ZG4
Plastic spur gear, Machined plastic (delrin)



CSSSS
Stainless steel spherical bearing, Stainless steel / PTFE



PSG05S
Spur gear - precision range, Stainless steel 316



SCE
U-shaped cable clamp, Steel



CHML50
Worm and wheel gear reducer, up to 107 Nm - Integrated



T5M_T10M
T type timing belt per metre, T5 Steel cored polyurethane



FF10
Offset spur gear reducer, from 0.78 to 3.70 Nm

Complementary products



PRF4545
Standard aluminium profile, 45 x 45 mm



RLXAC8
Free roller, Steel



RLX
Free running conveyor roller, PVC