



## For mounting additional panels

# MiniTecPRF<sub>BV</sub>


- For the addition of panels with a wall thickness of 2-6 mm
- Can be used with all solid panels (not mesh grills)
- Allow 2mm for assembly (reduce panel size to leave 1mm on each side)
- Material: arev polyamide


#### Assembly

- Mount the block in the profile slot at the required position
- Offer the pre-drilled panels into the aperture
- Secure the panels using suitable M6 screws
- Note: Hole distance, 7.5-16mm from edge









וח	C	_	n		N	_	•	
וע	3	U	v	U	IN	ш	3	

Qty.	1+	50+	100+		
Disc.	List	-5%	On request		

Part number	For profile	Weight (kg)	Stock*	Price each 1 to 49
PRF-BV	all types from PRF32	0,01	V	3,09 €

<sup>\*</sup>Depending on availability - Dimensions in mm







## Our other products



Adjustement bushing for half-rail guide, Adjustment bushing



Precision locknut, Precision locknut



Worm and wheel set, Machined plastic (delrin)



Roll-Ring® chain tensioner, Roll-Ring® Self-adjusting



Closed polymer Drylin® R bearing, Drylin® R



Worm and wheel set, Machined plastic (delrin)



Dual-thread screw wood/metal, Stainless steel



Plastic clamping collar, Ø10 - Ø20



Tool for thread repair inserts, Assembly tool



Linear bearing, Light



Self-centering flanged locking assembly,



Worm and wheel gear reducer, up to 28 Nm

## Complementary products



Standard aluminium profile, 45 x 45 mm