

Uses


- Low cost fastening requiring little preparation
- Used for different assembly types

Central hole


- Directly accepts M8 screws



Quick-fixing



1



2



3

Assembly

1. Tap the central hole of the first profile (1) using a fluteless M8 tap.
Lightly attach the fastener to the end of the profile using the M8 screw (do not screw in completely)
2. Attach the second profile (2) in the required position.
3. Tighten the M8 grub screw with an SW4 hexagonal key or the PRF-TOOL-H4 tool.
Max. Suggested torque 12Nm

Advantages

- Ends of profiles remain available
- Fastener is not visible
- Profiles can be repositioned/adjusted at any time
- Assembly will not twist
- Maximum load allowed: 6000N
- Cross joints in 3 dimensions can be created
- Joint can conduct electricity for bonding purposes.

Fastener for aluminium profile

Stock

PRF **MiniTec** Universal fastener
FIXUNI


Profile assembly

- Can be used to join all profile types
- Use multiple fasteners for longer lengths
- Materials:
- Fastener: electroplated chromed steel or stainless steel
- Round headed M8 screw, 25mm long.




Assembly

- Lightly attach the fastener into the slot on the profile (do not tighten)
- Slide the fastener in the slot to the required position
- Tighten the M8 grubscrew with an SW4 hexagonal key or the **PRF-TOOL-H4** tool



No drilling



DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	For profile	Tightening torque (Nm)	Weight (kg)	Stock*	Price each 1 to 49
PRF-FIX-UNI	All type of PRF profile	10,0	0,029	✓	5,56 €
PRF-FIX-UNI/SS	Stainless PRF/SS profile	01,2	-	-	12,27 €

*Depending on availability - Dimensions in mm

Our other products



BPM_LOK

Long-Lok slotted spring plunger with ball tip, LONG-LOK - Steel



B3PAN

Panamech, Multi-Beam stainless steel, Stainless steel - with clamping...



AT5courroie

AT type timing belt, AT5 Steel cored polyurethane



CHA_GC_9SS

Stainless steel garnet hinge, To be welded



LWL

Linear ball slide - Stainless steel balls, Rail - from 514 N to 1670...



MDR

Dee shackle with eye bolt, Steel




VLBS

Folding lifting ring for welding, Folding - for welding



HCSS

Set screw with hexagonal socket, Cup point



PB

Plastic deep groove ball bearing, Plastic -



GAC

Latch clamp with lock, Lockable



PLA

Flat magnet, Flat magnet with threaded



MEB

Moulded plastic bevel gear (nylon), 1:1

Complementary products



PRF1932

Standard aluminium profile, 19 x 32 mm



PRF4545

Standard stainless steel profile, 45 x 45 mm



PRF_FIX_STD

Fastener for aluminium profile, Standard fastener



PRF_FIX_ANG

Fastener for aluminium profile, Angular joint